

## General Information

<b>Extended Product Type:</b>	ZS4
<b>Product ID:</b>	1SNK505010R0000
<b>EAN:</b>	3472595050109
<b>Catalog Description:</b>	ZS4 Screw Clamp Terminal Block - Feed-through - Grey
<b>Long Description:</b>	- Save space by connecting conductors up to 4 mm <sup>2</sup> (without insulated ferrule, CB certified) 12 AWG in just 5.2 mm 0.205 in spacing, - Perfectly adapted to solar applications: voltage is rated 1000 V AC / DC IEC.

## Categories

Products » Low Voltage Products and Systems » Connection Devices » Terminal Blocks » SNK Series

## Ordering

<b>Minimum Order Quantity:</b>	50 piece
<b>Customs Tariff Number:</b>	85369010
<b>Color:</b>	Grey

## Dimensions

<b>Product Net Height:</b>	53 mm
<b>Product Net Length:</b>	47.3 mm
<b>Product Net Depth:</b>	47.3 mm
<b>Product Net Weight:</b>	8.8 g
<b>Product Net Width:</b>	5.2 mm

## Technical

<b>Spacing:</b>	5.2 mm
<b>Connection Type:</b>	Screw clamp
<b>Function:</b>	Feed-through
<b>Number of Levels:</b>	1
<b>Connecting Capacity Main Circuit:</b>	Screw Clamp / Flexible 1x 0.22 ... 4 mm <sup>2</sup> Screw Clamp / Flexible 2x 0.2 ... 1.5 mm <sup>2</sup> Screw Clamp / Rigid 1x 0.2 ... 4 mm <sup>2</sup> Screw Clamp / Rigid 2x 0.2 ... 1.5 mm <sup>2</sup> Screw Clamp / With Insulated Ferrule 1x 0.22 ... 2.5 mm <sup>2</sup> Screw Clamp / Without Insulated Ferrule 1x 0.22 ... 4 mm <sup>2</sup> Screw Clamp / With Twin Ferrule 2x 0.22 ... 1.5 mm <sup>2</sup>
<b>Gauge Type:</b>	A3-B3
<b>Rated Current (I<sub>n</sub>):</b>	Main Circuit 32 A
<b>Rated Short-time Withstand Current (I<sub>cw</sub>):</b>	for 1 s 480 A
<b>Rated Voltage (U<sub>r</sub>):</b>	1000 V
<b>Rated Impulse Withstand Voltage (U<sub>imp</sub>):</b>	8000 V
<b>Dielectric Test Voltage:</b>	2200 V
<b>Pollution Degree:</b>	3
<b>Power Loss:</b>	1 W
<b>Degree of Protection:</b>	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
<b>Insulation Material:</b>	Polyamide
<b>Mounting on DIN Rail:</b>	TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
<b>Wire Stripping Length:</b>	10.5 mm
<b>Recommended Screw Driver:</b>	3.5 mm
<b>Rated Cross-Section:</b>	4 mm <sup>2</sup>

## Technical UL/CSA

<b>Connecting Capacity Main Circuit UL/CSA:</b>	Screw Clamp / Flexible 1x 24 ... 12 AWG Screw Clamp / Flexible 2x 24 ... 16 AWG Screw Clamp / Rigid 1x 24 ... 12 AWG Screw Clamp / Rigid 2x 24 ... 16 AWG Screw Clamp / With Insulated Ferrule 1x 24 ... 14 AWG Screw Clamp / Without Insulated Ferrule 1x 24 ... 12 AWG Screw Clamp / With Twin Ferrule 2x 24 ... 16 AWG
<b>Connecting Capacity UL/CSA:</b>	Stranded 12 AWG
<b>Flammability According to UL94:</b>	V0

**Short-Circuit Current Rating (SCCR):** 100 kA  
**Maximum Operating Voltage** Main Circuit 600 V  
**UL/CSA:**

## Environmental

**Resistance to Vibrations acc. to IEC 60068-2-6:** Compliant

**RoHS Status:** Following EU Directive 2002/95/EC August 18, 2005 and amendment

**Ambient Air Temperature:** Operation -55 ... +110 °C  
Storage -55 ... +110 °C

## Certificates and Declarations (Document Number)

**Instructions and Manuals:** 1SNK160027C0201

**ATEX Certificate:** 1SND162004A1706

**BV Certificate:** 1SND161073A0203

**CB Certificate:** 1SND161017A0202

**CSA Certificate:** 1SND161070A0208

**cUL Certificate:** 1SND161040A0206

**Data Sheet, Technical Information:** 1SNK161001D0201

**Declaration of Conformity - CE:** 1SND225112U1000

**DNV Certificate:** 1SND161087A0202

**EAC Certificate:** 1SND161010A1100

**RINA Certificate:** 1SND161088A0200

**RoHS Information:** 1SND230491F0206

## Classifications

**E-nummer:** 2925900

**ETIM 4:** EC000897 - Feed-through terminal block

**ETIM 5:** EC000897 - Feed-through terminal block

**ETIM 6:** EC000897 - Feed-through terminal block

**Object Classification Code:** X

## Container Information

**Package Level 1 Width:** 54 mm

**Package Level 1 Length:** 252 mm

**Package Level 1 Height:** 52 mm

**Package Level 1 Gross Weight:** 0.44 kg

**Package Level 1 EAN:** 3472595050109

**Package Level 2 Units:** 900 piece

**Package Level 2 Width:** 300 mm

**Package Level 2 Length:** 400 mm

**Package Level 2 Height:** 200 mm

**Package Level 2 Gross Weight:** 8.420 kg

**Package Level 3 Units:** 43200 piece

**Product Packing Type:** Box

**Package Level 1 Units:** 50 piece

