

## Pillar slewing crane with electric chain hoist

swivel range approx. 300°

**DEMAG**

### Application:

For the lifting and moving of heavy workpieces of all kinds. Materials can be rapidly transported and accurately lowered within a certain radius. Column required for the assembly of a crane system if structural conditions mean there are no other options. Rated according to DIN 15018 H2 B3 and UVV-BGV D6 for operation in production halls.

### Execution:

- Robust column with long-lasting geometry
- Boom with hollow profile rails and extremely smooth running chassis
- Complete with electric chain hoist DC-Com, hook displacement 4 m, see no. 77099 012-020
- Power supply: Tow line
- Colour: RAL 1007, daffodil yellow, boom powder-coated, column painted with one-coat 2K lacquer

### Advantage:

- Extremely smooth running of the hoist in the hollow rail specially designed for transporting tasks
- Protected against soiling
- Easy swivelling thanks to low tare weight of boom

### Delivery:

Column, boom, chassis, electrical fittings or power supply, hoist



<b>Art. no.</b>	<b>77111 257</b>
<b>Brand</b>	DEMAG
<b>Load-carrying capacity</b>	500 kg
<b>Overhang</b>	3 m
<b>Lower edge of crane bottom</b>	2736 mm
<b>Construction height</b>	3499 mm
<b>Lifting device design</b>	DEMAG chain hoist DC-Com, DC 5-500 single chain
<b>Swivel range</b>	300 Degree
<b>Colour</b>	Daffodil yellow RAL 1007
<b>Product category</b>	B2B produkt
<b>Gross weight</b>	281 kg
<b>Gross Weight</b>	281.000 kg
<b>Product Group</b>	774

