Ultra Green SMD LED - 0603 multicomp PRO



Specifications:

| Dice Material |
|-------------------------|
| Emitted Colour |
| Lens Colour |
| Peak Wavelength |
| Viewing Angle |
| Luminous Intensity (IV) |
| Package Size |

- : InGaN
- : Ultra Green
- : Water Clear
- : 520nm
- : 130 Deg.
- : 1090mcd
- 1.00000000
- : 1.6mm × 0.8mm × 0.6mm, SMD LED 0603

RoHS

Compliant

Absolute Maximum Ratings (T_a = 25°C)


| Reverse Voltage | 5 Volt | | |
|---|---------------------|--|--|
| Reverse Current | 10µA (Vr = 5V) | | |
| Electrostatics Discharge (ESD) | 200 Volt | | |
| Operating Temperature Range | -40°C to +85°C | | |
| Storage Temperature Range | -40°C to +100°C | | |
| Lead Soldering Temperature Range (1.6mm (1/16 inch) from body) | 260°C for 5 Seconds | | |

Electrical/Optical Characteristics at Ta = 25°C

| Parameter | Symbol | Minimum | Typical | Maximum | Unit | Test |
|---|-----------|---------|---------|---------|---------|-----------|
| Luminous Intensity | IV | 700 | 1090 | 1360 | mcd | |
| Viewing Angle | 20 1/2 | | 130 | | Degrees | |
| Peak Emission Wavelength | λP | | 520 | | | IF = 20mA |
| Dominant Wavelength | λD | 520 | 526 | 532 | nm | |
| Spectral Line Half-Width | Δλ | | 36 | | | |
| Forward Voltage | VF | 2.8 | 2.9 | 3.2 | V | IF = 20mA |
| Power Dissipation | Pd | | | 85 | mW | |
| Peak Forward Current (Duty 1/10 at 1kHz) | IF (Peak) | | | 100 | mA | |
| Recommended Operating Current | IF (Rec) | | 20 | | mA | |


Typical Electro-Optical Characteristics Curves

Ultra Green (InGaN λP = 525nm)




Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro





Diagram



Recommended soldering pad design

Dimensions : Millimetres Tolerance: ±0.2mm

Part Number Table

| Description | Part Number |
|---|-------------|
| 1.6mm × 0.8mm × 0.6mm, SMD LED - 0603, Ultra Green, Water Clear, Cut Tape | MC011365 |
| 1.6mm × 0.8mm × 0.6mm, SMD LED - 0603, Ultra Green, Water Clear, Tape and Reel | MC011367 |

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro

