


## BXT ML4 BD 5 (920 340)


- LifeCheck SPD monitoring function
- Optimal protection of two pairs
- For installation in conformity with the lightning protection zone concept at the boundaries from  $0_A -2$  and higher



Figure without obligation



Basic circuit diagram BXT ML4 BD 5



Dimension drawing BXT ML4 BD 5

Space-saving combined lightning current and surge arrester module with LifeCheck feature for protecting two pairs of unearthed balanced interfaces. If LifeCheck detects thermal or electrical overload, the arrester has to be replaced. This status is indicated contactlessly by the DEHNrecord LC / SCM / MCM reader.

Type	BXT ML4 BD 5
Part No.	920 340
SPD monitoring system	LifeCheck
SPD class	TYPE 1 Pt
Nominal voltage ( $U_N$ )	5 V
Max. continuous operating voltage (d.c.) ( $U_C$ )	6.0 V
Max. continuous operating voltage (a.c.) ( $U_C$ )	4.2 V
Nominal current at 45 °C ( $I_N$ )	1.0 A
D1 Total lightning impulse current (10/350 $\mu$ s) ( $I_{imp}$ )	10 kA
D1 Lightning impulse current (10/350 $\mu$ s) per line ( $I_{imp}$ )	2.5 kA
C2 Total nominal discharge current (8/20 $\mu$ s) ( $I_n$ )	20 kA
C2 Nominal discharge current (8/20 $\mu$ s) per line ( $I_n$ )	10 kA
Voltage protection level line-line for $I_{imp}$ D1 ( $U_p$ )	$\leq 25$ V
Voltage protection level line-PG for $I_{imp}$ D1 ( $U_p$ )	$\leq 550$ V
Voltage protection level line-line at 1 kV/ $\mu$ s C3 ( $U_p$ )	$\leq 9$ V
Voltage protection level line-PG at 1 kV/ $\mu$ s C3 ( $U_p$ )	$\leq 550$ V
Series resistance per line	1.0 ohm(s)
Cut-off frequency line-line ( $f_c$ )	1.0 MHz
Capacitance line-line (C)	$\leq 5.4$ nF
Capacitance line-PG (C)	$\leq 16$ pF
Operating temperature range ( $T_U$ )	-40 °C ... +80 °C
Degree of protection (with plugged-in protection module)	IP 20
Pluggable into	BXT BAS / BSP BAS 4 base part
Earthing via	BXT BAS / BSP BAS 4 base part
Enclosure material	polyamide PA 6.6
Colour	yellow
Test standards	IEC 61643-21 / EN 61643-21
SIL classification	up to SIL3 <sup>*)</sup>
ATEX approvals	DEKRA 11ATEX0089 X: II 3 G Ex nA IIC T4 Gc
IECEx approvals	DEK 11.0032X: Ex nA IIC T4 Gc
CSA & USA Hazloc approvals (1)	2516389: Class I Div. 2 GP A, B, C, D T4
CSA & USA Hazloc approvals (2)	2516389: Class I Zone 2, AEx nA IIC T4
Weight	23 g
Customs tariff number	85363010
GTIN	4013364108967
PU	1 Stk

<sup>\*)</sup>For more detailed information, please visit [www.dehn-international.com](http://www.dehn-international.com).

We reserve the right to introduce changes in performance, configuration and technology, dimensions, weights and materials in the course of technical progress. The figures are shown without obligation.