

## Miniature cutting insert type AU HW56 15

For longitudinal inside boring

**ATORN**<sup>®</sup>

### Application

For longitudinal internal boring in steel and (stainless steel) material groups at low to high cutting speeds and mid-range cutting conditions.

### Version

- Solid carbide cutting insert with 90° attack angle with internal cooling

### Advantage

- Very hard cemented carbide grade ensures low wear
- Stable geometry optimised for internal boring machining
- Extremely sharp cutters ensure a process-reliable cut



<b>Art. no.</b>	<b>17122 272</b>
<b>ISO name</b>	AU
<b>Shaft diameter</b>	6 mm
<b>Length</b>	51 mm
<b>Clearance length</b>	22 mm
<b>Radius</b>	0.15 mm
<b>Programming size 2</b>	0.9 mm
<b>Programming size</b>	2.8 mm
<b>Min. bore diameter</b>	6.1 mm
<b>Holder size</b>	6
<b>Machining direction</b>	Right
<b>Carbide type</b>	HW56 15
<b>Material to be processed</b>	Stainless steel, Non-ferrous metal

### EAN-Code

405029337426 1