

Collet chuck extension

With internal cooling and straight shank

diebold

Application:

For clamping tools with a straight shank.

Execution:

- With straight shank, type ER standard.
- Particularly slim version for use in milling chucks as tool extension for deep machining operations where space is restricted.
- Wrench no. 23308 008 and collets 23320.
- Wrench no. 23308 008 and collets 23320.

Delivery:

1x collet chuck extension.



Art. no.	23304 240
Brand	DIEBOLD
Manufacturer Part Number	74.010.240
Collet type	ER 25
Shank diameter	20 mm
Min./max. clamping range	1-16 mm
Outer diameter	42 mm
Shaft length	50 mm
Length of head	46 mm
Gross Weight	0.347 kg
Product Group	2AB