

## Lever gauge

MarTest



### Application:

For measuring deviations in concentricity, axial run-out, parallelism and flatness. For centring shafts, boreholes and aligning workpieces.

### Execution:

- Impact-resistant movement
- Dial sealed with O-ring
- Anti-magnetic components
- Automatic switching of callipers direction
- Measuring element supported in 8 precious stones
- 3 dovetail mounting surfaces

### Advantage:

- Viewing window made of mineral glass, therefore resistant to solvents



<b>Art. no.</b>	<b>33303 050</b>
<b>Brand</b>	MAHR
<b>Manufacturer Part Number</b>	4301250
<b>Length measuring range</b>	0.5 mm
<b>Scale value</b>	0.01 mm
<b>Measurement force</b>	0.1 N
<b>Length of measuring sensor from centre of ball</b>	14.5 mm
<b>Material of measuring ball</b>	Carbide
<b>Ball diameter</b>	2 mm
<b>Pivot range of measuring sensor</b>	220 Degree
<b>Diameter</b>	38 mm
<b>Connection thread</b>	M2
<b>DIN</b>	2270
<b>Calibration Group</b>	L
<b>Gross Weight</b>	0.168 kg
<b>Product Group</b>	305

### EAN

4059192013134