Service

Rexroth Bosch Group

RE 10227/12.10 1/24 Replaces: 04.07

Internal gear pump, fixed displacement

Type PGH

Frame size 4 and 5 Component series: 3X Maximum operating pressure 350 bar Maximum displacement volume 250 cm³



Contents	Page
Features	1
Ordering code single pumps	2
Function, section, symbol	3
Technical data	4 and 5
Characteristic curves	On request
Unit dimensions single pumps	6 to 11
Ports	12
Pump combinations	13
Unit dimensions pump combinations	14 to 18
Project planning information	19 to 22
Commissioning notes	23

Features

-	Fixed	disp	lacement
---	-------	------	----------

- Low operating noise
- Little flow pulsation
- High efficiency also at low speed and viscosity due to sealing gap compensation

H7417_d

- Suitable for broad viscosity and speed ranges
- All frame sizes and sizes can be combined with each other in any form
- Can be combined with internal gear pumps, vane pumps and axial piston pumps
- Suitable for operation with HFC fluid (seal design "W")
- Use:

For fatigue-resistant drives with high power and high pressures with very large load cycle numbers, e.g. plastics processing machines, automated presses, foundry machines and other applications with accumulator charging operation.

Information on available spare parts: www.boschrexroth.com/spc

Ordering code: Single pumps

											Т		-				
		PG	H		<u>-</u> 3X/							*	_				
Series High pres	ssure pump	=	: H										Fu	Irther		s in the p e of con	
Frame si BG4 BG5	ze	amponent eorie	=	= 4 = 5	ov						J2 = E4 =			ISO 4	2-hole 1-hole cordir	mountin mountin ng to ISO nd VDM/	g flang g flang) 3019-
(30 to 39:		omponent serie i installation ar ns) Displaceme	nd	39 = .	3X				V = W =							FK ng made	
0.20	Size	revolution											(ren	nainin	g sea	ls made	of FKN
BG4	20 25 32	20.10 cm ³ 25.30 cm ³ 32.70 cm ³	3		= 020 = 025 = 032			07 = 11 =			S				andarc	le conne I pressur I-pressur	e serie
	40 50	40.10 cm ³ 50.70 cm ³	3		= 040 = 050		E =									Су	desig
BG5	63	64.70 cm ³			= 063		R =									AE involu	-
	80 100 125	81.40 cm ³ 100.20 cm 125.30 cm	3 3		= 080 = 100 = 125	R		[Direc	tio	n o	f ro			-	at the sh Cl vise (on ו	ockwis
	160 200 250	162.80 cm 200.40 cm 250.50 cm	3		= 160 = 200 = 250	1	-						lindri		naft (a	ccording	-

Not all variants are possible according to the type key! Please select the desired pump using the selection tables (pages 6 to 11) or after consultation with Bosch Rexroth.

²⁾ In case of operation with HFC fluid

³⁾ For each size, one type of connection **07** or **11** has been determined:

- 07: PGH5-3X/200/250...
- 11: PGH4-3X/020/025/032/040/050...

PGH5-3X/063/080/100/125/160...

The suction ports have all been designed in standard pressure series (dimensions see page 12).

Standard types PGH4-3X								
Туре	Material no.							
PGH4-3X/020RE11VU2	R901147100							
PGH4-3X/025RE11VU2	R901147101							
PGH4-3X/032RE11VU2	R901147102							
PGH4-3X/040RE11VU2	R901147103							
PGH4-3X/050RE11VU2	R901147104							


Standard types PGH5-3X								
Туре	Material no.							
PGH5-3X/063RE11VU2	R901147115							
PGH5-3X/080RE11VU2	R901147116							
PGH5-3X/100RE11VU2	R901147117							
PGH5-3X/125RE11VU2	R901147118							
PGH5-3X/160RE11VU2	R901147119							
PGH5-3X/200RE07VU2	R901147120							
PGH5-3X/250RE07VU2	R901147121							

Function, section, symbol

Structure

Hydraulic pumps of type PGH.-3X are gap-compensated internal gear pumps with fixed displacement.

They mainly consist of: Mounting flange (1), housing (2),



Suction and displacement procedure

The hydro-dynamically mounted pinion shaft (4) drives the toothed internal gear (5) in the direction of rotation shown.


The tooth clearances opening in the suction area prime the fluid. The fluid is transported into the tooth clearances of pinion and internal gear, from the suction area (S) into the pressure area (P).

There, the fluid is displaced from the closing tooth clearances and delivered into the pressure port (P).


Suction and discharge area are separated by the radial compensation elements (9 to 11) and the tooth engagement between internal gear and pinion shaft.

Axial compensation

The displacement chamber in the pressure area is axially sealed by axial washers (7).




The sides of the axial washers facing away from the displacement area are backed by a pressure field (12). These fields balance the axial washers vis-à-vis the displacement area, which results in a perfect sealing with low mechanical losses. cover with through-drive (3), pinion shaft (4), internal gear (5), sliding bearings (6), axial washers (7) and stop pin (8) as well as the radial compensation consisting of segment (9), segment support (10) and the seal rolls (11).



Radial compensation

The radial compensation elements consist of segment (9), segment support (10) and seal rolls (11).

Segment (9) and segment support (10) are arranged in the pressure field so that the resulting compressive force is basically accepted by the stop pin.



A small compressive force component presses segment and segment support onto the tooth tips of pinion shaft and internal gear and in this way provides for the separation of the pressure area from the suction area with automatic clearance adjustment.

This is the prerequisite for constantly high volumetric efficiency during the entire operating time.

The clearance adjustment of segment and segment support is made possible by the seal rolls located inbetween.

Hydro-dynamic and hydrostatic mounting

The pinion shaft (4) is accepted by hydro-dynamically lubricated radial sliding bearings (6).

The internal gear (5) is mounted hydrostatically in the housing.

Gearing

The gearing with involute edges has a large meshing length for little flow and pressure pulsation and thus guarantees lownoise running.

Technical Data (For applications outside these parameters, please consult us!)

general

Internal gear pump, gap-compensated
SAE 2-hole flange according to ISO 3019-1 or 4-hole flange according to VDMA 24560 and ISO 3019-2
Flange port
Radial and axial forces (e.g. belt pulley) only after coordination
Clockwise or counterclockwise (on request) – not bidirectional!

hydraulic

Hydraulic fluid			HLP – mineral oil according to DIN 51524 part 2 HFC – water polymer solutions according to DIN EN ISO 12922 ^{1) 2)} : Seal design W HEES – fluids according to DIN ISO 15380 ¹⁾ HFD-U – fluids according to VDMA 24317 ¹⁾ , DIN EN ISO 12922 ¹⁾ Please observe our specifications according to data sheet RE 90220 Other fluids on request!
Hydraulic fluid	HLP fluid	°C	-10 to +80; for other temperatures please consult us!
temperature range	Special fluid	°C	-10 to +50; for other temperatures please consult us!
Ambient temperatu	re range	°C	-20 to +60
Viscosity range		mm²/s	10 to 300 (to n = 1800 min ⁻¹) 10 to 100 (to n = 3000 min ⁻¹) 2000 admissible start viscosity (400 to 1800 min ⁻¹)
Max. admissible lev hydraulic fluid cleanliness class a			Class 20/18/15 ³⁾

¹⁾ Attention!

To these media, the limitations for special fluids apply

- ²⁾ Hydraulic fluid HFC: Input speed n_{max} = 2000 min⁻¹
- ³⁾ The cleanliness classes specified for the components must be adhered to in hydraulic systems. Efficient filtration prevents failures and simultaneously increases the service life of the components.

For the selection of filters, see data sheets RE 50070, RE 50076, RE 50081, RE 50086 and RE 50088.

Technical Data (For applications outside these parameters, please consult us!)

Frame size	Frame size	e	PGH4						
Size	Size		20		25	32	4	.0	50
Weight	т	kg	14	1	4.5	15	1	6	17
Speed range 1)	n _{min}	min ⁻¹	200	2	200	200	2	00	200
	n _{max}	min ⁻¹	3000		000	3000	30	00	3000
Displacement	V	cm ³	20.1	2	25.3	32.7	40).1	50.7
Flow ²⁾	q_{V}	l/min	28.9	3	36.3	46.9	57	7.6	72.8
Moment of inertia (around drive axis)	J	kgm ²	0.0003	7 0.0	0045	0.00055	0.00	0066	0.00081
Power consumption	P _{ad}	kW							
Min. drive power necessar	y (with $p \approx 1$	bar)	1.1		1.1	1.1	1	.1	1.5
Max. admissible drive pow	er		35		44	56	6	51	76
Operating pressure, absolute – Input	р р	bar		0	.8 to 2 (sh	ortly, upon	start 0.6 b	ar)	
Nominal pressure	, p _N	bar							
- Output, continuous	HLP fluid				315	5			250
	Special flu	iid ³⁾			220)			175
intermittent ⁴⁾						315			
	Special flu	iid ³⁾			245	5			210
Frame size	Frame size	e				PGH5		I	
Size	Size		63	80	100	125	160	200	250
Weight	т	kg	42	43.5	45.5	48	52	55.5	60.5
Speed range 1)	n _{min}	min ⁻¹	200	200	200	200	200	200	200
	n _{max}	min ⁻¹	3000	3000	3000	3000	3000	3000	3000
Displacement	V	cm ³	64.7	81.4	100.2	125.3	162.8	200.4	250.5
Flow ²⁾	q_{V}	l/min	92.8	116.9	143.8	179.8	233.7	287.7	359.6
Moment of inertia (around drive axis)	J	kgm ²	0.00237	0.00289	0.00329	0.00407	0.00506	0.00623	0.00760
Power consumption	$P_{\rm ad}$	kW							
Min. drive power necessar	y (with $p \approx 1$	bar)	1.8	2.2	3	4	5.5	7.5	7.5
Max. admissible drive pow	er		96	103	129	161	134	140	134
Operating pressure, absolute – Input	р р	bar		0	.8 to 2 (sho	ortly, upon	start 0.6 b	ar)	
Nominal pressure	p _N	bar				· · ·			
 Output, continuous 	HLP fluid			31	5		210	170	135
	Special flu	iid ³⁾	id ³⁾ 220 145 115					115	90
intermittent ⁴) p _{max} bar									
internition	HLP fluid			35	50		260	210	170

¹⁾ Hydraulic fluid HFC: Input speed $n_{max} = 2000 \text{ min}^{-1}$ ²⁾ Measured with $n = 1450 \text{ min}^{-1}$, $p = 10 \text{ bar and} = 30 \text{ mm}^2/\text{s}$

³⁾ Attention!


To these media, the limitations for special fluids apply ⁴⁾ Max 10 s, max. 50 % of the duty cycle

Unit dimensions of frame size 4 (dimensions in mm [inch])

PGH4-3X/...^RE...VU2

Drive shaft cylindrical, SAE 2-hole mounting flange

	Material no.	"L" counter-					
Type Size	"R" clockwise	clockwise	L1	L2	L3	S ¹⁾	P ¹⁾
PGH4-3X/020E11VU2	R901147100	On request	145	70.5	129	1" S	3/4" H
FGH4-3X/020E11V02	N901147100	On request	[5.71]	[2.78]	[5.08]	13	3/4 П
PGH4-3X/025E11VU2	R901147101	On request	150	73	134	1 1/4" 0	3/4" H
PGH4-3X/025E11V02	R901147101	On request	[5.91]	[2.87]	[5.28]	1 1/4" S	3/4 П
PGH4-3X/032E11VU2	R901147102	Oranaat	157	76.5	141	1 1/2" S	1" H
PGH4-37/032E11V02	R901147102	On request	[6.18]	[3.01]	[5.55]	11/2 5	
	D001147102	On request	164	80	148	1 1/0" 0	1" H
PGH4-3X/040E11VU2	R901147103	On request	[6.46]	[3.15]	[5.83]	1 1/2" S	
	D001147104	On request	174	85	158	2" S	
PGH4-3X/050E11VU2	R901147104	On request	[6.85]	[3.35]	[6.22]	23	1" H



¹⁾ S = Standard pressure series;

H = High-pressure series;

exact dimensions see table page 12


²⁾ For multiple pumps, the combination part starts from here

The figure shows a pump with clockwise rotation, in case of pumps with counterclockwise rotation, the pressure port is on the opposite side!

Unit dimensions of frame size 4 (dimensions in mm [inch])

PGH4-3X/... RE...VE4 Drive shaft cylindrical, 4-hole mounting flange according to ISO 3019-2 and VDMA 24560

	Material no.						
Type Size	"R" clockwise	L1	L2	L3	S ¹⁾	P ¹⁾	
PGH4-3X/020RE11VE4	D001147105	145	70.5	129	1" S	3/4" H	
PGH4-37/020RE11VE4	R901147105	[5.71]	[2.78]	[5.08]	13	3/4" H	
PGH4-3X/025RE11VE4	R901147106	150	73.0	134	1 1/4" S	3/4" H	
FGH4-37/025hE11VE4		[5.91]	[2.87]	[5.28]	1 1/4 3		
	D001147107	157	76.5	141	1 1/0" 0	1" H	
PGH4-3X/032RE11VE4	R901147107	[6.18]	[3.01]	[5.55]	1 1/2" S		
PGH4-3X/040RE11VE4	D001147100	164	80	148	1 1/2" S	1" H	
PGH4-3X/040RETTVE4	R901147108	[6.46]	[3.15]	[5.83]	11/2 5		
PGH4-3X/050RE11VE4	R901147109	174	85	158	2" S	-1" LI	
		[6.85]	[3.35]	[6.22]	23	1" H	



¹⁾ S = Standard pressure series;

H = High-pressure series;

exact dimensions see table page 12

²⁾ For multiple pumps, the combination part starts from here


Unit dimensions of frame size 4 (dimensions in mm [inch])


PGH4-3X/...RR...VU2

Drive shaft splined, SAE 2-hole mounting flange

(central and back pump in pump combinations)

	Mater						
Type Size	"R" clockwise	"L" counter- clockwise	L1	L2	L3	S ¹⁾	P ¹⁾
	D001147110		145	70.5	129	1".0	0/4"
PGH4-3X/020R11VU2	R901147110	On request	[5.71]	[2.78]	[5.08]	1" S	3/4" H
	D001147114	On request	150	73	134	4 4 / 4 11 0	3/4" H
PGH4-3X/025R11VU2	R901147111		[5.91]	[2.87]	[5.28]	1 1/4" S	
	D001117110		157	76.5	141	4.4/01.0	1" H
PGH4-3X/032R11VU2	R901147112	On request	[6.18]	[3.01]	[5.55]	1 1/2" S	
	D001117110	0	164	80	148	4.4/01.0	4 7 1 1
PGH4-3X/040R11VU2	R901147113	On request	[6.46]	[3.15]	[5.83]	1 1/2" S	1" H
	D001147114	Ora war and a	174	85	158	0" 0	4 7 1 1
PGH4-3X/050R11VU2	R901147114	On request	[6.85]	[3.35]	[6.22]	2" S	1" H





Shaft 25-4; SAE J/44 JU Involute gear ANSI B92.1a-1976, 15T 16/32 DP 30°

¹⁾ S = Standard pressure series;

H = High-pressure series;

exact dimensions see table page 12

²⁾ For pump combinations, the combination part starts from here


The figure shows a pump with clockwise rotation, in case of pumps with counterclockwise rotation, the pressure port is on the opposite side!

Unit dimensions of frame size 5 (dimensions in mm [inch])

PGH5-3X/... ^R E...VU2

Drive shaft cylindrical, SAE 2-hole mounting flange

		Mater	rial no.					
Туре	Size	"R" clockwise	"L" counter- clockwise	L1	L2	L3	S ¹⁾	P ¹⁾
		D001147115		210	105.5	194	2" S	4 4 / 4 11 11
PGH5-37	(/063E11VU2	R901147115	On request	[8.27]	[4.15]	[7.64]	23	1 1/4" H
		D001147116		218	109.5	202	2" S	1 1/4" LI
PGH5-37	(/080E11VU2	R901147116	On request	[8.58]	[4.31]	[7.95]	23	1 1/4" H
	(/100E11VU2	R901147117		227	114	211	2 1/2" S	1 1/2" H
PGH0-37	V100E11V02	H901147117	On request	[8.94]	[4.49]	[8.31]	21/25	
	(/125E11VU2	R901147118		239	120	223	2 1/2" S	1 1/2" H
FGH5-37	V125E11VU2	N901147110	On request	[9.41]	[4.72]	[8.78]	21/23	Т 1/2 П
	(/160E11VU2	R901147119	On request	257	129	241	3" S	2" H
FGH5-37	V160E11V02	N901147119	On request	[10.12]	[5.08]	[9.49]	33	2 П
		D001147100		275	138	259	0.1/0" €	2" S
PGH0-37	(/200E07VU2	R901147120	On request	[10.83]	[5.43]	[10.20]	3 1/2" S	23
	(/250E07VU2	P001147101	On request	299	150	283	2 1/0" 6	0 1/0" 6
	V230E07V02	R901147121	On request	[11.77]	[5.91]	[11.14]	3 1/2" S	2 1/2" S



¹⁾ S = Standard pressure series;

- H = High-pressure series;
- exact dimensions see table page 12

 $^{\mbox{\tiny 2)}}$ For pump combinations, the combination part starts from here


The figure shows a pump with clockwise rotation, in case of pumps with counterclockwise rotation, the pressure port is on the opposite side!


Unit dimensions of frame size 5 (dimensions in mm [inch])

PGH5-3X/...RE...VE4

Drive shaft cylindrical, 4-hole mounting flange according to ISO 3019-2 and VDMA 24560

		Material no.					
Type Size		"R" clockwise	L1	L2	L3	S ¹⁾	P ¹⁾
PGH5-3X/063R		R901147122	210	105.5	194	2" S	1 1/4" H
FGH5-37/003h		N301147122	[8.27]	[4.15]	[7.64]	2.5	I 1/4 П
PGH5-3X/080R		R901147123	218	109.5	202	2" S	1 1/4" H
FGH3-37/060h		N901147123	[8.58]	[4.31]	[7.95]	25	11/4 П
PGH5-3X/100R		R901147124	227	114	211	2 1/2" S	1 1/2" H
FGH3-37/100h		N901147124	[8.94]	[4.49]	[8.31]	21/2 3	Т 1/2 П
PGH5-3X/125R		R901147125	239	120	223	2 1/2" S	1 1/0" Ц
FGHJ-37/123h		N901147125	[9.41]	[4.72]	[8.78]	21/23	1 1/2" H
PGH5-3X/160R		R901147126	257	129	241	3" S	o" ⊔
PGH5-37/160K		H901147120	[10.12]	[5.08]	[9.49]	33	2" H
PGH5-3X/200R		R901147127	275	138	259	0.1/0" 6	0" 0
PGH5-37/200K	EU7 VE4	H901147127	[10.83]	[5.43]	[10.20]	3 1/2" S	2" S
		D001147100	299	150	283	0.1/0" 0	0.1/0" 0
PGH5-3X/250R		R901147128	[11.77]	[5.91]	[11.14]	3 1/2" S	2 1/2" S





¹⁾ S = Standard pressure series;

H = High-pressure series;

exact dimensions see table page 12

 $^{\mbox{\tiny 2)}}$ For pump combinations, the combination part starts from here


Unit dimensions of frame size 5 (dimensions in mm [inch])


PGH5-3X/...^RR...VU2

Drive shaft splined, SAE 2-hole mounting flange

(central and back pump for pump combinations)

Material no.		ial no.					
		"L" counter-					
Type Size	"R" clockwise	clockwise	L1	L2	L3	S ¹⁾	P ¹⁾
PGH5-3X/063R11VU	2 R901147129	On request	219	114.5	203	2" S	1 1///" 凵
	11301147123	On request	[8.62]	[4.51]	[7.99]	2.0	P ¹⁾ 1 1/4" H 1 1/4" H 1 1/2" H 1 1/2" H 2" H 2" S 2 1/2" S
PGH5-3X/080R11VU2	2 R901147130	On request	227	118.5	211	2" S	1 1/ <i>4</i> " LI
FGH5-37/060h11V02	L 1901147130	On request	[8.94]	[4.67]	[8.31]	23	1 1/4" H
PGH5-3X/100R11VU	2 R901147131		236	123	220	2 1/2" S	1 1/0" Ц
PGH5-37/100R11V02	1901147131	On request	[9.29]	[4.84]	[8.66]	21/2 3	I 1/2 П
	D001147100	On request	248	129	232	0.1/0" 6	1 1/2" H
PGH5-3X/125R11VU2	2 R901147132	On request	[9.76]	[5.08]	[9.13]	2 1/2" S	
PGH5-3X/160R11VU	2 R901147133	On request	266	138	250	3" S	0" Ц
PGH5-3A/160R11V02	1 R901147133	On request	[10.47]	[5.43]	[9.84]	33	2 П
	D001147104	On request	284	147	268	2 1/0" 6	0" 6
PGH5-3X/200R07VU2	2 R901147134	On request	[11.18]	[5.79]	[10.55]	3 1/2" S	2"5
	D001147105	On request	308	159	292	0.1/01/0	0.1/0".0
PGH5-3X/250R07VU2	2 R901147135	On request	[12.13]	[6.26]	[11.50]	3 1/2" S	21/2 5






¹⁾ S = Standard pressure series;


- H = High-pressure series;
- exact dimensions see table page 12

 $^{\mbox{\tiny 2)}}$ For pump combinations, the combination part starts from here

The figure shows a pump with clockwise rotation, in case of pumps with counterclockwise rotation, the pressure port is on the opposite side!


Ports (dimensions in mm [inch])






Frame size	Size	Porting pattern/ suction port S	D1	D2	S1	S2	Porting pattern/ pressure port P	D3	D4	P1	P2
	020	1" 5000 PSI	Ø25 [Ø0.984]	M10; 18	52.4 [2.063]	26.2 [1.032]	3/4" 6000 PSI	Ø19 <i>[Ø0.748]</i>	M10; 18	50.8 [2.000]	23.8 [0.937]
	025	1 1/4" 4000 PSI	Ø32 [Ø1.260]	M10; 18	58.7 [2.311]	30.2 [1.189]	3/4" 6000 PSI	Ø19 <i>[Ø0.748]</i>	M10; 18	50.8 [2.000]	23.8 [0.937]
4	032	1 1/2" 3000 PSI	Ø38 [Ø1.496]	M12; 21	69.9 [2.752]	35.7 [1.406]	1" 6000 PSI	Ø25.4 [Ø1.000]	M12; 23	57.2 [2.252]	27.8 [1.094]
	040	1 1/2" 3000 PSI	Ø38 [Ø1.496]	M12; 21	69.9 [2.752]	35.7 [1.406]	1" 6000 PSI	Ø25.4 [Ø1.000]	M12; 23	57.2 [2.252]	27.8 [1.094]
	050	2" 3000 PSI	Ø51 <i>[Ø2.008]</i>	M12; 21	77.8 [3.063]	42.9 [1.689]	1" 6000 PSI	Ø25.4 [Ø1.000]	M12; 23	57.2 [2.252]	27.8 [1.094]
	063	2" 3000 PSI	Ø51 <i>[Ø2.008]</i>	M12; 21	77.8 [3.063]	42.9 [1.689]	1 1/4" 6000 PSI	Ø32 [Ø1.260]	M12; 21	66.6 [2.622]	31.8 <i>[1.252]</i>
	080	2" 3000 PSI	Ø51 <i>[Ø2.008]</i>	M12; 21	77.8 [3.063]	42.9 [1.689]	1 1/4" 6000 PSI	Ø32 [Ø1.260]	M12; 21	66.6 [2.622]	31.8 [1.252]
	100	2 1/2" 2500 PSI	Ø64 [2.520]	M12; 23	88.9 [3.500]	50.8 [2.000]	1 1/2" 6000 PSI	Ø38 [Ø1.496]	M16; 30	79.3 [3.122]	36.5 [1.437]
5	125	2 1/2" 2500 PSI	Ø64 [2.520]	M12; 23	88.9 [3.500]	50.8 [2.000]	1 1/2" 6000 PSI	Ø38 [Ø1.496]	M16; 30	79.3 [3.122]	36.5 [1.437]
	160	3" 2000 PSI	Ø76 [Ø2.992]	M16; 30	106.4 <i>[4.189]</i>	61.9 <i>[2.437]</i>	2" 6000 PSI	Ø51 <i>[Ø2.008]</i>	M20; 35	96.8 [3.811]	44.5 [1.752]
	200	3 1/2" 500 PSI	Ø89 [Ø3.504]	M16; 30	120.7 [4.752]	69.9 [2.752]	2" 3000 PSI	Ø51 <i>[Ø2.008]</i>	M12; 23	77.8 [3.063]	42.9 [1.689]
	250	3 1/2" 500 PSI	Ø89 [Ø3.504]	M16; 30	120.7 <i>[4.752]</i>	69.9 [2.752]	2 1/2" 2500 PSI	Ø64 [Ø2.520]	M12; 23	88.9 [3.500]	50.8 [2.000]


Measuring port PGH4-3X/... and PGH5-3X/...








Transport thread PGH5-3X/...



Pump combinations

All internal gear pumps of type PGH-3X can be combined; each pump has an output shaft gearing. The combination options and the material numbers of the necessary combination parts are shown in the following figure. Please observe the project planning information for pump combinations on page 21.

	Front pump	Mater	ial no.
Back pump		PGH4-3X	PGH5-3X
PGH2-2X/RU2	(RE10223)	R901155288	R901155283
PGH3-2X/RU2	(RE10223)	R901155288	R901155283
PGH4-3X/RU2		R901155289	R901155284
PGH5-3X/RU2		-	R901155285
PGF2-2X/JU2	(RE10213)	R901155288	R901155283
PGP2-2X/JU2	(RE10231)	R901155288	R901155283
PGF3-3X/JU2	(RE10213)	R901155287	R901155282
PGP3-3X/JU2	(RE10231)	R901155287	R901155282
PVV/Q1-1X/JB	(RE10335)	R901155287	R901155282
PVV/Q2-1X/JB	(RE10335)	R901155287	R901155282
PVV/Q4-1X/JC	(RE10335)	-	R901155286
PVV/Q5-1X/JC	(RE10335)	-	R901155286
AZPF-1X/RRB	(RE10089)	R901155288	R901155283



L = Counterclockwise (on request)

¹⁾ For detailed information refer to the ordering code page 2

²⁾ In connection with cylindrical and splined shaft


³⁾ Only in connection with cylindrical shaft (according to VDMA); only with clockwise rotation


Order example:

P3GH5-3X/160+GH5-3X/100+GH4-3X/050REVE4

The dimensional drawings show the front pump and the combination part.

Combination part PGH5-3X+GF3-3X/VV1-1X/VV2-1X/K02 Material no.: **R901155282**





PGH5-3X Size	PGH5-3X/REU2 PGH5-3X/REE4 L1	PGH5-3X/RRU2 L1
63	264 [10.39]	273 [10.75]
80	272 [10.71]	281 <i>[11.06]</i>
100	281 <i>[11.06]</i>	290 <i>[11.42]</i>
125	293 [11.54]	302 [11.89]
160	311 <i>[12.24]</i>	320 <i>[12.60]</i>
200	329 <i>[12.95]</i>	338 <i>[13.31]</i>
250	353 <i>[13.90]</i>	362 [14.25]


PGF3/PGP2 Size	L2	L3
20	144.5 <i>[5.69]</i>	79.5 <i>[3.13]</i>
22	146.5 <i>[5.77</i>]	80.5 <i>[3.17]</i>
25	150.5 <i>[5.93]</i>	82.5 <i>[3.25]</i>
32	159.5 <i>[6.28]</i>	87 <i>[3.43]</i>
40	169.5 <i>[6.67</i>]	92 <i>[3.62]</i>

PVVUMB Frame size	L2	L3 (P)	L4 (S)
1	156 <i>[6.14]</i>	133 <i>[5.24]</i>	63.5 <i>[2.50]</i>
2	163 <i>[6.42]</i>	38 [1.50]	120.5 <i>[4.75]</i>

The dimensional drawings show the front pump and the combination part.

Combination part PGH5-3X+GH2/3-2X/GF2-2X/AZPF-1X/K01

Material no.: R901155283



PGH5-3X Size	PGH5-3X/REU2 PGH5-3X/REE4 L1	PGH5-3X/RRU2 L1
63	241 <i>[9.49]</i>	250 <i>[9.84]</i>
80	249 [9.80]	258 [10.16]
100	258 [10.16]	267 [10.51]
125	270 [10.63]	279 [10.98]
160	288 [11.34]	297 [11.69]
200	306 <i>[12.05]</i>	315 <i>[12.40]</i>
250	330 <i>[12.99]</i>	339 <i>[13.35]</i>

PGH2		
Size	L2	L3
005	110 <i>[4.33]</i>	54 <i>[2.13]</i>
006	112.5 <i>[4.43]</i>	55.5 [2.19]
008	116 [4.57]	57 [2.24]

PGH3		
Size	L2	L3
011	121.5 <i>[4.78]</i>	60 <i>[2.36]</i>
013	126.5 <i>[4.98]</i>	62.5 <i>[2.46]</i>
016	131.5 <i>[5.18]</i>	65 <i>[2.56]</i>


PGF2/PGP2		
Size	L2	L3
006	116 <i>[4.567]</i>	65 <i>[2.559]</i>
008	119.5 <i>[4.705]</i>	67 <i>[2.638]</i>
011	125 <i>[4.921]</i>	69.5 <i>[2.736]</i>
013	130 <i>[5.118]</i>	72 [2.835]
016	135 <i>[5.315]</i>	74.5 [2.933]
019	141 <i>[5.551]</i>	77.5 [3.051]
022	147 <i>[5.787]</i>	80.5 <i>[3.169]</i>

AZPF		
Size	L2	L3
004	85 <i>[3.346]</i>	40 <i>[1.575]</i>
005	87.5 <i>[3.445]</i>	41 <i>[1.614]</i>
008	91.5 <i>[3.602]</i>	43 [1.692]
011	96.5 <i>[3.799]</i>	47 [1.850]
014	101.5 <i>[3.996]</i>	47.5 [1.870]
016	105 <i>[4.134]</i>	47.5 <i>[1.870]</i>
019	110 <i>[4.331]</i>	47.5 <i>[1.870]</i>
022	115.5 <i>[4.547]</i>	55 <i>[2.165]</i>

The dimensional drawings show the front pump and the combination part.

Combination part PGH5-3X+GH4-3X..R

Material no.: R901155284



V	iew	


PGH5-3X Size	PGH5-3X/REU2 PGH5-3X/REE4 L1	PGH5-3X/RRU2 L1
63	264 [10.39]	273 [10.75]
80	272 [10.71]	281 <i>[11.06]</i>
100	281 <i>[11.06]</i>	290 [11.42]
125	293 [11.54]	302 [11.89]
160	311 <i>[12.24]</i>	320 <i>[12.60]</i>
200	329 [12.95]	338 <i>[13.31]</i>
250	353 <i>[13.90]</i>	362 [14.25]

PGH4-3XRU2 Size	L2	L3
20	145 <i>[5.71]</i>	70.5 <i>[2.78]</i>
25	150 <i>[5.91]</i>	73 [2.87]
32	157 <i>[6.18]</i>	76.5 <i>[3.01]</i>
40	164 <i>[6.46]</i>	80 <i>[3.15]</i>
50	174 <i>[6.85]</i>	85 <i>[3.35]</i>

The dimensional drawings show the front pump and the combination part.

Combination part PGH5-3X+GH5-3X..R

Material no.: R901155285




View X

PGH5-3X Size	PGH5-3X/REU2 PGH5-3X/REE4 L1	PGH5-3X/RRU2 L1
63	264 [10.39]	273 [10.75]
80	272 [10.71]	281 <i>[11.06]</i>
100	281 <i>[11.06]</i>	290 <i>[11.42]</i>
125	293 [11.54]	302 <i>[11.89]</i>
160	311 <i>[12.24]</i>	320 <i>[12.60]</i>
200	329 <i>[12.95]</i>	338 <i>[13.31]</i>
250	353 <i>[13.90]</i>	362 [14.25]

PGH5-3XRU2		
Size	L2	L3
63	219 <i>[8.62]</i>	114.5 <i>[4.51]</i>
80	227 [8.94]	118.5 <i>[4.67]</i>
100	236 <i>[9.29]</i>	123 <i>[4.84]</i>
125	248 [9.76]	129 <i>[5.08]</i>
160	266 [10.47]	138 <i>[5.43]</i>
200	284 [11.18]	147 <i>[5.79]</i>
250	308 <i>[12.13]</i>	159 <i>[6.26]</i>

The dimensional drawings show the front pump and the combination part.

Combination part: PGH5-3X+VV4/5-1X..J Material no. R901155286



PGH5-3X Size	PGH5-3X/REU2 PGH5-3X/REE4 L1	PGH5-3X/RRU2 L1
63	264 [10.39]	273 [10.75]
80	272 [10.71]	281 <i>[11.06]</i>
100	281 <i>[11.06]</i>	290 <i>[11.42]</i>
125	293 [11.54]	302 [11.89]
160	311 <i>[12.24]</i>	320 <i>[12.60]</i>
200	329 <i>[12.95]</i>	338 <i>[13.31]</i>
250	353 <i>[13.90]</i>	362 [14.25]

PVVUMB Frame size	L2	L3 (P)	L4 (S)
4	186 <i>[7.32]</i>	38 [1.50]	126 <i>[4.96]</i>
5	216 [8.50]	43 [1.69]	153 <i>[6.02]</i>

1. General notes

This project planning information refers to the specific properties of the Rexroth PGH.-3X internal gear pump.

Comprehensive general information and suggestions are contained in the hydraulics trainer, edition 3 "Project planning information and design of hydraulic systems", RE 00281.

1.1 Intended use

Rexroth internal gear pumps are intended for the setup of hydraulic drive systems in the fields of machine and plant construction. During project planning, the basic principles of the EU Machinery Directive or comparable national regulations outside the EU have to be observed.

The pumps must not be used in explosive environments in accordance with directive 94/9/EC (ATEX).

1.2 Technical data

The system or machine manufacturer has to ensure compliance with the admissible technical data and operating conditions. The pump itself does not contain a device to prevent operation outside the admissible data.

All mentioned technical features are average values and are applicable for the specified boundary conditions. In case of modifications to the boundary conditions (e.g. viscosity), the technical data may change as well. Tolerances corresponding to the relevant state-of-the-art are possible.

Operating the pump outside of the admissible technical data (pages 4, 5) is possible to a certain extent, however, this requires the explicit written approval by Bosch Rexroth.


2. Hydraulic project planning

2.1 Bleeding option for commissioning

For Rexroth internal gear pumps PGH.-3X a manual, switchable or automatic bleeding option is to be provided for the initial commissioning or re-commissioning after maintenance and repair works. As bleeding point, the measurement port (M) available at the pump can be used. Otherwise, the bleeding point has to be put into the pressure line in front of the first valve or check valve. Bleeding may be effected with a maximum counter-pressure of 0.2 bar.

Examples of bleedings circuits:

- 1. Automatic bleeding via automatic bleeding valve
- 2. Switchable bleeding
- 3. Manually operated bleeding



2.2 Suction line

The line cross-sections have to be dimensioned for the designed flows in a manner that an ideal suction speed of 0.6 to 1.2 m/s is achieved on average. The suction speed must not exceed a maximum value of 2 m/s.


The suction cross-sections at the pump itself are dimensioned for the maximum flow and thus are a reference only. In case of continuous operation with speeds lower than the admissible maximum speed, the suction tube diameter is to be dimensioned smaller than the suction port of the pump in accordance with the actual suction speed.

All in all, the suction line has to be designed in a way that the admissible inlet operating pressure is complied with (0.8 to 2 bar absolute)! Bends and a combination of the suction tubes of several pumps must be avoided. If suction filters have to be used, it has to be ensured on the system side that the lowest admissible inlet operating pressure is not exceeded even when the filter is contaminated.

Please ensure air tightness of the transitions and dimensional stability of the suction hose as regards to the external air pressure.

The suction tube immersion depth should be selected as large as possible. Depending on the internal reservoir pressure, the viscosity of the operating medium, and the flow ratios within the reservoir, no vortex must be formed even during maximum flow. Otherwise there is the risk of sucking in air.

We recommend selecting suction tubes according to AB 23-03.



2.3 Pressure line

With pressure lines, sufficient bursting resistance of the tubes, hoses and connection elements has to be ensured. The cross-sections should be based on the maximum flow in order to avoid additional excessive load of the pump due to backpressure. In this connection, you must also consider the pipe losses across the entire pressure line length and other line resistances (e.g. bends, pressure filters).

2.4 Pressure limitation

The internal gear pump PGH is not equipped with devices for compliance with the maximum operating pressure. Setting and limiting the admissible operating pressure has to be ensured on the system side.

The pressure relief valves necessary for that purpose are to be designed considering the maximum flow and the existing pressure increase speed so that the admissible intermittent operating pressure is not exceeded.

2.5 Pressure holding function

In the variable-speed drive, the pump can temporarily also be operated below the specified minimum speed, in the pressure holding function. The holding time and the related necessary speed result from the operating viscosity and the pressure level. For the design, please contact Bosch Rexroth's Technical Sales.

In the deactivated condition (speed = 0), a leakage flow flows through the pump back into the reservoir, depending on the load pressure. If this is to be securely prevented, a check valve has to be used.

When using a check valve, please observe the information on bleeding in chapter 2.1.

3. Mechanical project planning

3.1 Installation and disassembly option

For installing and disassembling the pump on or from the drive, accessibility has to be provided for on the system side by means of suitable lifting gear. Please consider especially the own weight of frame size PGH 5 (see "Technical Data", page 5).

Screws of the property class 8.8 or 10.9 have to be provided for mounting purposes.

3.2 Mounting

On the machine side, the screws have to be accessible in a way that the required tightening torque can be applied. The tightening torque is based on the operating conditions and involved elements of the screw connection and has to be specified by the manufacturer in the power unit, machine or system project planning.

3.3 Reservoir

In the reservoir construction or the selection of suitable standard reservoirs, the following requirements are to be observed:

- Selection of the largest reservoir volume possible, depending on the continuous or average flow, in order to allow for the separation of air bubbles by means of enough dwell time of the medium in the reservoir. In this connection, the air separation capability of the fluid used is also important.
- Provision of settling zones for the fluid in the reservoir in order to allow for air separation.
- Provision of guiding plates in order to allowing for the deposit of contamination at the reservoir bottom outside the pump suction area.
- Large dimensioning of the reservoir surfaces depending on the heat output to be dissipated via the reservoir walls.

3.4 Required power unit functions

Hydraulic power units should at least be equipped with the following features:

- Reservoirs, the internal pressure of which corresponds to the ambient pressure in accordance with the design, have to be equipped with ventilation filters for pressure compensation purposes.
- The fluid should be filled by means of filling connections only excluding filling with unfiltered fluid.
- Pollution or humidity must be prevented from getting into the system. When using the pump in a highly polluted environment, the reservoir is to be pre-tensioned by means of air pressure for this. If cleansing of the external reservoir side is intended or to be expected during the period of use, reservoir fittings for tubes, lines, or hoses have to be selected, which ensure safe seal against external pressurization with water jet.


3.5 Place of installation and ambient conditions

With places of installation from a geodetic height of more than 1000 m, the pump is to be arranged in or below the reservoir or the reservoir is to be pre-tensioned by means of compressed air in order to comply with the admissible minimum inlet pressure. The suction line is to be selected short and with a large cross-section, bends should not be used.

When installing the pump more than 10 m below the reservoir, the reduction of the inlet pressure to the maximum admissible value has to be ensured by means of additional measures.

When operating the pump in salt-containing or corrosive environments or when pressurization with strongly abrasive substances is possible, it has to be ensured on the system side that the shaft seal ring and the sealing area of the shaft do not make direct contact with the environment.


3.6 Installation positions



4. Pump combinations

- It has to be ensured with pump combinations that the operating data admissible for the relevant pump type is complied with in every stage.
- The combined pumps must all have the same direction of rotation.
- The pump with the largest torque, variable displacement pumps or pumps with intermittent load are to be provided as first stage in the pump combination.
- The maximum through-drive torque must be checked by the project planner for every application. This also applies to already existing (encoded) pump combinations.

Maximum admissible torques in Nm:



Attention!

Installation position motor at bottom and pump at top (e.g. IM V2) is not admissible!

• A pump stage drive torque is calculated as follows:

$$T = \frac{\Delta p \cdot V \cdot 0.0159}{\eta_{\text{hydr.-mech.}}}$$

- T: Torque in Nm
- Δp : Operating pressure in bar
- V: Displacement in cm³
- η: Hydraulic-mechanical efficiency

Туре	Drive torque		Output torque
	Cylindrical shaftE	Splined shaftR	
PGH4	450	450	280
PGH5	1100	1400	700

- The total of the torques in a pump combination must not exceed the max. drive torque.
- · Joint aspiration is not possible.
- For reasons of stability, we recommend the ISO 4-hole mounting flange according to VDMA "E4" for combinations of three and more pumps
- Before operating pump combinations with different mediums, please consult Bosch Rexroth.
- Central and back pumps must have the shaft design "R" (splined).

5. Maintenance schedule and operational safety

For safe operation and a long service life of the pump, a maintenance schedule has to be developed for the power unit, the machine, or the system. The maintenance schedule has to ensure that the intended or admissible operating conditions of the pump are complied with during the period of use.

In particular, compliance with the following operating parameters has to be ensured:

- The required oil cleanliness
- The operating temperature range
- The level of the operating medium

Furthermore, the pump and the system have to be checked for modifications of the following parameters on a regular basis:

- Vibrations
- Noise
- Temperature difference pump fluid in the reservoir
- Foam formation in the reservoir
- Leak-proofness

Modifications of these parameters indicate wear of components (e.g. drive motor, coupling, pump, etc.). The cause has to be determined and remedied immediately.

In order to achieve high operational safety of the pump in the machine or system, we recommend checking the parameters mentioned above continuously and automatically and shutting the system down automatically in case of modifications exceeding the usual fluctuations in the intended operating range.

Plastic components of drive couplings should be replaced regularly, however, after 5 years at the latest. The corresponding information of the manufacturer is to be observed.

For preventive maintenance of the pump, we recommend having the seals replaced after a maximum operating period of 5 years by an authorized Bosch Rexroth service company.

6. Accessories

6.1 SAE connection flanges

We recommend selecting the SAE flanges for suction and pressure port according to AB 22-15 (with welded connection) or AB 22-13 (with threaded connection).

6.2 Pump safety block

For limiting the operating pressure and for the pump circulation at zero pressure, we recommend our pump safety blocks type DBA... according to RE 25890.

Automatic bleeding upon commissioning is, however, not possible via DBA blocks. In this connection, we recommend a separate manual or automatic bleeding, e.g. via the pump's measurement port (see page 19)!

6.3 Other accessories

To install the Rexroth PGH.-3X internal gear pump on electric motors, we recommend selecting the pump mounting brackets according to AB 41-20 and torsionally flexible couplings according to AB 33-22.

Commissioning notes

Preparation

- Check whether the system has been installed carefully and cleanly.
- Only fill in hydraulic fluid in through a filter with the required minimum retention rate.
- Via suction or pressure pipe, fill the pump completely with the hydraulic fluid.
- Check the direction of rotation for compliance with the direction of rotation according to the pump type.

Bleeding

- Open the bleed port at the system or switch to circulation at zero pressure, according to the system operating instructions. During bleeding, discharge of enclosed air at zero pressure must be guaranteed.
- For bleeding the pump, switch the pump on and immediately off again (jog mode). This process is to be repeated until complete bleeding of the pump is ensured.
- Close the manually opened bleed ports again.

Commissioning

- If complete bleeding of the pump has been ensured, switch on the motor. Let the pump run at zero pressure until the system is completely bled. For the bleeding of the system, the system operating instructions are to be observed.
- Commission the system according to the system operating instructions and load the pump.
- After some operating time, check the hydraulic fluid in the reservoir for bubble or foam formation at the surface.

Operation

- Pay attention to changes in the noise characteristic during operation. Due to heating of the operating medium, minor noise increases are normal. Considerable increase in the noise or random short-term changes in the noise may be an indication of the aspiration of air. If the suction tubes are too short or the operating medium filling levels are too low, air can also be sucked in via a vortex.
- Changes in operating speeds, temperatures, noise increase or power consumption are an indication of wear or damage at the system or the pump.

Re-commissioning

- Check the pump and the system for leakage. Leaks are an indication of leakage below the hydraulic fluid level. An increased hydraulic fluid level in the reservoir is an indication of leakage above the hydraulic fluid level.
- If the pump is arranged above the hydraulic fluid level, the pump may run empty due to leakage, e.g. a worn shaft seal. In this case, the system must be bled once again during re-commissioning. Provide for repair.
- After repair and maintenance works, you must bleed the system once again.
- If the system is intact, switch on the motor.

General

- The pumps supplied by us have been tested for function and performance. Modifications of any type at the pump are not permitted since this would result in the invalidation of warranty claims!
- Repairs may only be carried out by the manufacturer or their authorized dealers and agencies. Repairs carried out by the customer are not covered by a warranty.

A Important notes

- The pump may only be installed, maintained and repaired by authorized, trained and instructed personnel!
- The pump may only be operated within the admissible data (see page 4 and 5)!
- The pump may only be operated if it is in an unobjectionable condition!
- When carrying out any work on the pump, depressurize the system!
- Unauthorized conversions or modifications, which affect safety and function are not permitted!
- Protective devices (e.g. coupling protection) are to be attached and/or existing protective devices must not be removed!
- Make sure that all mounting screws are always properly tightened! (Observe the prescribed tightening torque!)
- The generally valid safety and accident prevention regulations must imperatively be complied with!

Bosch Rexroth AG Hydraulics Zum Eisengießer 1 97816 Lohr am Main, Germany Phone +49 (0) 93 52 / 18-0 Fax +49 (0) 93 52 / 18-23 58 documentation@boschrexroth.de www.boschrexroth.de

© This document, as well as the data, specifications and other information set forth in it, are the exclusive property of Bosch Rexroth AG. It may not be reproduced or given to third parties without its consent. The data specified above only serve to describe the product. No statements concerning a certain condition or suitability for a certain application can be derived from our information. The information given does not release the user from the obligation of own judgment and verification. It must be remembered that our products are subject to a natural process of wear and aging.