


CORE DIMENSIONS:

A	25.91 [1.020]	+	0.46 [.018]
B	13.06 [.514]	+	0.25 [.010]
C	28.58 [1.125]	+	0.64 [.025]
D	12.95 [.510]	+	0.18 [.007]

IMPEDANCE (Z)			
Frequency	25 MHz	100 MHz	300 MHz
Nominal (REF)	130 Ω	280 Ω	440 Ω
Minimum	- Ω	224 Ω	- Ω

Z vs. FREQUENCY
(REF. ONLY)




AGILENT E4991A Impedance/Material Analyzer
HP 16092A-Test Fixture, REF 3158

UNCONTROLLED DOCUMENT

NOTES:

1. ASSEMBLED PART #: 28A2024-0A2
2. CASE COLOR: BLACK.
3. CASE FLAMMABILITY RATING: UL94 V-2.
4. CASE MATERIAL: Halogen Free Nylon



CASE DIMENSIONS:

A	29.00 [1.142]	+	REF.
B	13.00 [.512]	+	REF.
C	32.50 [1.280]	+	REF.
D	29.62 [1.166]	+	REF.
E	5.64 [.222]	+	REF.

DIMENSIONS ARE IN mm[INCHES].				This print is the property of Laird Tech. and is loaned in confidence subject to return upon request and with the understanding that no copies shall be made without the written consent of Laird Tech. All rights to design or invention are reserved.			Laird TECHNOLOGIES®		
F	UPDATED NOTE 3	09/15/10	JUN	PROJECT/PART NUMBER: 28A2024-0A2			REV	PART TYPE:	DRAWN BY:
E	UPDATE COMPANY LOGO ADD NOTES 3&4	01/27/09	JRK				F	FERRITE SNAP ON	JRK
D	UPDATE 100 MHz MINIMUM VALUE CORRECT CASE DIM "B" TOLERANCE SYMBOL	06/07/07	TMB				DATE:	SCALE:	MATERIAL:
C	UPDATE COMPANY LOGO	04/18/07	TMB				06/29/04	NTS	NiZn FERRITE
B	UPDATE "D" DIM ON CASE REVISE NOTES	08/24/06	TMB				CAD #	TOOL #	
A	ORIGINAL DRAFT	06/29/04	JRK				28A2024-0A2-F	-	
REV	DESCRIPTION	DATE	INT						