
## Electrical Testing per Tusonix standard test plans and Mil-Std-202 Test Methods.


## MARKETING SALES DRAWING

DIMENSIONS IN INCHES - DO NOT SCALE THIS DRAWING DIMENSIONS IN METRIC - [ ]



WIDDLE GROUND CIRCUIT





## NOTES:

- TUSONIX STANDARD PART NUMBER: 4100-053.
   TUSONIX RoHS COMPLIANT PART NUMBER: 4100-053 LF.
   CUSTOMER MUST SPECIFY STANDARD OR RoHS PART NUMBER WHEN ORDERING.
- 2. LEAD FINISH: STANDARD PART #: 60/40 SOLDER PLATED. RoHS PART #: SILVER PLATED.
- 3. PART MARKING: STANDARD PART: NO MARKING.
  RoHS PART: GREEN INK DOT ON INSULATION BAND.

			Cx Iz @ 2	2	WORKING +85°C 250 @ 60 Hz VAC			+125°C 200 VDC		IR 10 G	CURREN Idc (A)				IB) PEF	INSERTION R MIL-STD-2 100 MHz 60			
X-2015 Rev-0 REVISION RECORD	0	WAS SK 6871-001. EC 07-27-88	1	REVISED & :R SK 6905-000.	2	200 WAS .175.	3	FMT.	-01 4		-02 5			DE	-TOLERANCES Jnless Otherwise Specified ECIMAL ± .031 [0.79]		P.C. BOARD MOUNT TYPE LOW PASS FILTER		FILTER
	I do			COMPLETELY F REDRAWN PER L.E. 09-29-88	170	DIM. REVISED L.E. 11-10-89	4900	RDN TO COMP   S.M. 05-09-00	20000508-2	ADDED NOTES S.M. 05-24-05	20050513-2			7	TUSON ICSON, ARI		Approv	1.0.	-08-00 05-08-00 1100-05