

Product characteristics

Inductive sensor

Plastic housing Ø 34 mm

Cable

Sensing range 20 mm; [nrf] non-flush mountable

Electrical data

Electrical design

Operating voltage [V]

Protection class

Reverse polarity protection

Outputs

Output function

Voltage drop [V]

Minimum load current [mA]

Leakage current [mA]

Current rating

- Current rating (continuous) [mA]

- Current rating (peak) [mA]

Short-circuit proof

Overload protection

Switching frequency [Hz]

Range

Sensing range [mm]

Real sensing range (Sr) [mm]

Operating distance [mm]

Accuracy / deviations

Correction factors

Hysteresis [% of Sr]

Switch-point drift [% of Sr]

Environment

Ambient temperature [°C]

Protection

Tests / approvals

EMC

MTTF [Years]

Mechanical data

Mounting

Housing materials

Weight [kg]

Displays / operating elements

Output status indication LED

Electrical connection

AC/DC

20...250 AC/DC

II

no

normally open

< 6.5 AC / < 6 DC

5

< 1 (250 V AC) / < 0.8 (140 V AC) / < 0.8 (24 V DC)

250 AC / 100 DC; 350 AC (...50 °C)

î: 2.2 A (20 ms / 0.5 Hz)

no

no

25 AC / 60 DC

20

20 ± 10 %

0...16.2

mild steel = 1 / stainless steel approx. 0.7 / brass approx. 0.5 / Al approx. 0.5 / Cu approx. 0.4

3...15

-10...10

-25...80

IP 67

EN 60947-5-2

EN 55011:

class B

611

non-flush mountable

housing: PBT; end cap: TPE

0.256

yellow

IB0078 - Inductive sensor - eclass: 27270101 / 27-27-01-01


| | |
|------------|--|
| Connection | PVC cable / 2 m; 2 x 0.5 mm ² |
|------------|--|

Wiring

Core colours

BN brown

BU blue



Note: miniature fuse to IEC60127-2 sheet 1,
≤ 2 A (fast acting)

| | |
|-------------|----------------|
| Accessories | Mounting clamp |
|-------------|----------------|

| | |
|------------------------|----------------|
| Accessories (included) | Mounting clamp |
|------------------------|----------------|

| | |
|---------|---|
| Remarks | Recommendation: check the unit for reliable function after a short circuit. |
|---------|---|

| | |
|---------|---|
| Remarks | Recommendation: check the unit for reliable function after a short circuit. |
|---------|---|

| | |
|---------------|-----------|
| Pack quantity | [piece] 1 |
|---------------|-----------|