

SFH 4259

Power TOPLED® Lens

High Power Infrared Emitter (850 nm)



Applications

- Electronic Equipment
- Industrial Automation (Machine controls, Light barriers, Vision controls)
- Remote Control, Proximity, Ambient Light Sensing
- Safety systems and CCTV

Features:

- Package: Epoxy, diffuse
- Qualifications: The product qualification test plan is based on the guidelines of AEC-Q101-REV-C, Stress Test Qualification for Automotive Grade Discrete Semiconductors.
- ESD: 2 kV acc. to ANSI/ESDA/JEDEC JS-001 (HBM, Class 2)
- High Power Infrared LED
- Half angle: $\pm 25^\circ$
- High forward current allowed at high temperature
- Short switching times

Ordering Information

Type	Radiant intensity ¹⁾ $I_F = 100 \text{ mA}; t_p = 20 \text{ ms}$ I_e	Radiant intensity ¹⁾ typ. $I_F = 100 \text{ mA}; t_p = 20 \text{ ms}$ I_e	Ordering Code
SFH 4259-Z	32 ... 100 mW/sr	55 mW/sr	Q65110A2464
SFH 4259-T2U	32 ... 80 mW/sr	55 mW/sr	Q65111A4857
SFH 4259-UV1	40 ... 100 mW/sr	55 mW/sr	Q65111A6098
SFH 4259-U	40 ... 80 mW/sr	55 mW/sr	Q65111A9681

Maximum Ratings

$T_A = 25 \text{ }^\circ\text{C}$

Parameter	Symbol	Values
Operating temperature	T_{op}	min. -40 °C max. 100 °C
Storage temperature	T_{stg}	min. -40 °C max. 100 °C
Reverse voltage ²⁾	V_R	max. 12 V
Forward current	I_F	max. 100 mA
Surge current $t_p \leq 100 \mu\text{s}; D = 0$	I_{FSM}	max. 1 A
Power consumption	P_{tot}	max. 180 mW
ESD withstand voltage acc. to ANSI/ESDA/JEDEC JS-001 (HBM, Class 2)	V_{ESD}	max. 2 kV

Characteristics

$I_F = 100 \text{ mA}$; $t_p = 20 \text{ ms}$; $T_A = 25^\circ\text{C}$

Parameter	Symbol	Values
Peak wavelength	λ_{peak}	typ. 860 nm
Centroid wavelength	$\lambda_{\text{centroid}}$	typ. 850 nm
Spectral bandwidth at 50% $I_{\text{rel,max}}$	$\Delta\lambda$	typ. 30 nm
Half angle	φ	typ. 25 °
Dimensions of active chip area	$L \times W$	typ. 0.3 x 0.3 mm x mm
Rise time (10% / 90%) $I_F = 100 \text{ mA}$; $R_L = 50 \Omega$	t_r	typ. 12 ns
Fall time (10% / 90%) $I_F = 100 \text{ mA}$; $R_L = 50 \Omega$	t_f	typ. 12 ns
Forward voltage	V_F	typ. 1.5 V max. 1.8 V
Forward voltage $I_F = 1 \text{ A}$; $t_p = 100 \mu\text{s}$	V_F	typ. 2.4 V max. 3 V
Reverse current ²⁾ $V_R = 5 \text{ V}$	I_R	max. 10 μA typ. 0.01 μA
Total radiant flux ³⁾	Φ_e	typ. 70 mW
Radiant intensity ¹⁾ $I_F = 1 \text{ A}$; $t_p = 25 \mu\text{s}$	I_e	typ. 440 mW/sr
Temperature coefficient of brightness	TC_I	typ. -0.5 % / K
Temperature coefficient of voltage	TC_V	typ. -0.7 mV / K
Temperature coefficient of wavelength	TC_λ	typ. 0.3 nm / K
Thermal resistance junction ambient real ⁴⁾	R_{thJA}	max. 300 K / W
Thermal resistance junction solder point real ⁵⁾	R_{thJS}	max. 140 K / W

Brightness Groups


$T_A = 25^\circ\text{C}$

Group	Radiant intensity $I_F = 100 \text{ mA}; t_p = 20 \text{ ms}$ min. I_e	Radiant intensity $I_F = 100 \text{ mA}; t_p = 20 \text{ ms}$ max. I_e
T2	32 mW/sr	50 mW/sr
U	40 mW/sr	80 mW/sr
V1	63 mW/sr	100 mW/sr

Only one group in one packing unit (variation lower 2:1).


Relative Spectral Emission ^{6), 7)}

$I_{\text{rel}} = f(\lambda); I_F = 100 \text{ mA}; t_p = 20 \text{ ms}$




Radiation Characteristics ^{6), 7)}


$$I_{\text{rel}} = f(\phi)$$

**Forward current** ^{6), 7)}

$$I_F = f(V_F); \text{ single pulse; } t_p = 100 \mu\text{s}$$


**Relative Radiant Intensity** ^{6), 7)}

$$\frac{I_e}{I_e(100 \text{ mA})} = f(I_F); \text{ single pulse; } t_p = 25 \mu\text{s}$$




Max. Permissible Forward Current


$$I_{F,\max} = f(T_A); R_{\text{thJA}} = 300 \text{ K / W}$$


**Permissible Pulse Handling Capability**

$$I_F = f(t_p); \text{duty cycle } D = \text{parameter}; T_A = 25^\circ\text{C}$$

**Permissible Pulse Handling Capability**

$$I_F = f(t_p); \text{duty cycle } D = \text{parameter}; T_A = 85^\circ\text{C}$$




Dimensional Drawing ⁸⁾

GPLY6128

Approximate Weight: 37.0 mg**Package marking:** Cathode


Pin	Description
1	Cathode
2	Anode
3	Anode
4	Anode

Recommended Solder Pad⁸⁾



Reflow Soldering Profile

Product complies to MSL Level 2 acc. to JEDEC J-STD-020E




Profile Feature	Symbol	Pb-Free (SnAgCu) Assembly Minimum	Recommendation	Maximum	Unit
Ramp-up rate to preheat*) 25 °C to 150 °C			2	3	K/s
Time t_s $T_{S\min}$ to $T_{S\max}$	t_s	60	100	120	s
Ramp-up rate to peak*) $T_{S\max}$ to T_p			2	3	K/s
Liquidus temperature	T_L		217		°C
Time above liquidus temperature	t_L		80	100	s
Peak temperature	T_p		245	250	°C
Time within 5 °C of the specified peak temperature T_p - 5 K	t_p	10	20	30	s
Ramp-down rate* T_p to 100 °C			3	4	K/s
Time 25 °C to T_p				480	s


All temperatures refer to the center of the package, measured on the top of the component

* slope calculation DT/Dt: Dt max. 5 s; fulfillment for the whole T-range

Taping ⁸⁾




C63062-A3636-B4-03

Tape and Reel ⁹⁾**Reel dimensions [mm]**


A	W	N_{\min}	W_1	$W_{2\max}$	Pieces per PU
180 mm	$12 + 0.3 / - 0.1$	60	$12.4 + 2$	18.4	2000

Barcode-Product-Label (BPL)




OHA04563

Dry Packing Process and Materials ⁸⁾



Moisture-sensitive product is packed in a dry bag containing desiccant and a humidity card according to JEDEC-STD-033.

Transportation Packing and Materials ⁸⁾



Dimensions of transportation box in mm

Width	Length	Height
195 ± 5 mm	195 ± 5 mm	30 ± 5 mm

Notes

The evaluation of eye safety occurs according to the standard IEC 62471:2006 (photo biological safety of lamps and lamp systems). Within the risk grouping system of this IEC standard, the LED specified in this data sheet fall into the class **exempt group (exposure time 10000 s)**. Under real circumstances (for exposure time, conditions of the eye pupils, observation distance), it is assumed that no endangerment to the eye exists from these devices. As a matter of principle, however, it should be mentioned that intense light sources have a high secondary exposure potential due to their blinding effect. When looking at bright light sources (e.g. headlights), temporary reduction in visual acuity and afterimages can occur, leading to irritation, annoyance, visual impairment, and even accidents, depending on the situation.

For further application related informations please visit www.osram-os.com/appnotes

Disclaimer

Disclaimer

Language english will prevail in case of any discrepancies or deviations between the two language writings.

Attention please!

The information describes the type of component and shall not be considered as assured characteristics. Terms of delivery and rights to change design reserved. Due to technical requirements components may contain dangerous substances.

For information on the types in question please contact our Sales Organization.

If printed or downloaded, please find the latest version in the OSRAM OS Webside.

Packing

Please use the recycling operators known to you. We can also help you – get in touch with your nearest sales office.

By agreement we will take packing material back, if it is sorted. You must bear the costs of transport. For packing material that is returned to us unsorted or which we are not obliged to accept, we shall have to invoice you for any costs incurred.

Product safety devices/applications or medical devices/applications

OSRAM OS components are not developed, constructed or tested for the application as safety relevant component or for the application in medical devices.

In case Buyer – or Customer supplied by Buyer – considers using OSRAM OS components in product safety devices/applications or medical devices/applications, Buyer and/or Customer has to inform the local sales partner of OSRAM OS immediately and OSRAM OS and Buyer and /or Customer will analyze and coordinate the customer-specific request between OSRAM OS and Buyer and/or Customer.

Glossary

- 1) **Radiant intensity:** Measured at a solid angle of $\Omega = 0.01 \text{ sr}$
- 2) **Reverse Operation:** Reverse Operation of 10 hours is permissible in total. Continuous reverse operation is not allowed.
- 3) **Total radiant flux:** Measured with integrating sphere.
- 4) **Thermal resistance:** junction - ambient, mounted on PC-board (FR4), padsize 16 mm² each
- 5) **Thermal resistance:** junction - soldering point, of the device only, mounted on an ideal heatsink (e.g. metal block)
- 6) **Typical Values:** Due to the special conditions of the manufacturing processes of LED, the typical data or calculated correlations of technical parameters can only reflect statistical figures. These do not necessarily correspond to the actual parameters of each single product, which could differ from the typical data and calculated correlations or the typical characteristic line. If requested, e.g. because of technical improvements, these typ. data will be changed without any further notice.
- 7) **Testing temperature:** $T_A = 25^\circ\text{C}$
- 8) **Tolerance of Measure:** Unless otherwise noted in drawing, tolerances are specified with ± 0.1 and dimensions are specified in mm.
- 9) **Tape and Reel:** All dimensions and tolerances are specified acc. IEC 60286-3 and specified in mm.

Published by OSRAM Opto Semiconductors GmbH EU RoHS and China RoHS compliant product
Leibnizstraße 4, D-93055 Regensburg
www.osram-os.com © All Rights Reserved.



此产品符合欧盟 RoHS 指令的要求；
按照中国的相关法规和标准，不含有毒有害物质或元素。