

## Micrometer

With cylindrical and spherical measuring faces

Mitutoyo

### Application:

For measuring e.g. curved surfaces and wall thicknesses of pipes, bearings, rings, etc.

### Version:

- Semi-gloss chrome-plated scale drum and sleeve
- Carbide-tipped measuring faces
- Friction coupling for consistent, repeatable measuring force

### Delivery:

Includes box, setting standard (from 25 mm), adjustment wrench



<b>Art. no.</b>	<b>32016 622</b>
<b>Min./max. length measuring range</b>	0-25 mm
<b>Vernier scale</b>	0.01 mm
<b>Measuring surface depth</b>	9 mm
<b>Measuring spindle increments</b>	0.5 mm
<b>Measuring surface width x Measuring surface depth</b>	8 x 9 mm
<b>Spindle clamping</b>	Yes
<b>Error limit</b>	3 µm
<b>Display</b>	Nonius
<b>Calibration Group</b>	D
<b>Type</b>	D – with cylindrical anvil
<b>Min./max. measurement force</b>	3-8 N

### EAN-Code

4946368011196