

Material

70 EPDM 331

black

cross linking: peroxidic
75 +/- 5 Shore A at the test slab

revision index	revision date	page	1 / 3
3	9/9/2016		

Physical properties	nominal range	typical values	
Density DIN EN ISO 1183, 23 °C	1.09 ±0.02	1.09	g/cm ³
Hardness DIN ISO 7619-1, Shore A, 23 °C	75 ±5	75	Shore
Modulus 100 %, DIN 53504, S2, 23 °C	> 6.5	8	MPa
Tensile strength DIN 53504, S2, 23 °C	> 10	13.6	MPa
Elongation at Break DIN 53504, S2, 23 °C	> 150	174	%
Compression set DIN ISO 815, B, 24 h, 150 °C, 25 %	< 20	11	%
Compression set DIN ISO 815, B, 70 h, 150 °C, 25 %	< 25	17	%
Temperature range	-40°C to 150°C		

Declarations of conformity

	Country	Part	Remark	Expires	unlimited
(EG) 1935/2004	EU		food		<input checked="" type="checkbox"/>
(EG) 2023/2006 (GMP)	EU		(EG) 2023/2006 (GMP)		<input checked="" type="checkbox"/>
3-A Sanitary	USA	Seals	Class II	12 / 2019	<input type="checkbox"/>
ACS	F	O-Ring	Drinking water	10 / 2021	<input type="checkbox"/>
ADI Free			see certificate		<input checked="" type="checkbox"/>
AS/NZS 4020:2005	AUS	O-Ring	Drinking water	01 / 2022	<input type="checkbox"/>
BFR XXI, Kat 4	Ger		food		<input checked="" type="checkbox"/>
DIN EN 681	D	O-Ring	K 18 1612		<input checked="" type="checkbox"/>
FDA	USA	Seals	§ 177.2600		<input checked="" type="checkbox"/>
Kiwa	NL	O-Ring	K44812/06		<input checked="" type="checkbox"/>
KTW		O-Ring	surface treated	06 / 2021	<input type="checkbox"/>
NSF 51	USA	Seals	food		<input checked="" type="checkbox"/>

Freudenberg

Freudenberg Sealing Technologies
Global Material Technology
Wolfgang Becker

Telefon: +49 (0)6201/80-2893
Fax: +49 (0)6201/88-2893
Email: wolfgang.becker@FST.com



Material 70 EPDM 331

black

cross linking: peroxidic
75 +/- 5 Shore A at the test slab

revision index	revision date		page		
3	9/9/2016		2 / 3		
	Country	Part	Remark	Expires	unlimited
NSF 61	USA	O-Ring	Drinking water		<input checked="" type="checkbox"/>
ÖNORM B 5014	A	O-Ring	Oberwihl (D) & Castello Calepi (IT)	09 / 2021	<input type="checkbox"/>
RoHS			see certificate		<input checked="" type="checkbox"/>
UBA Leitlinie	D	O-Ring	Oberwihl (D) & Castello Calepi (IT)	09 / 2021	<input type="checkbox"/>
USP Chapter 87 (in vitro)	USA	Seals			<input checked="" type="checkbox"/>
USP Class VI Ch. 88 - 121 °C	USA	O-Ring			<input checked="" type="checkbox"/>
W270	D	O-Ring	Drinking water	09 / 2021	<input type="checkbox"/>
WRAS BS 6920	GB	O-Ring	85 °C	01 / 2022	<input type="checkbox"/>

Freudenberg

Freudenberg Sealing Technologies
Global Material Technology
Wolfgang Becker

Telefon: +49 (0)6201/80-2893
Fax: +49 (0)6201/88-2893
Email: wolfgang.becker@FST.com



Material 70 EPDM 331

black

cross linking: peroxidic
75 +/- 5 Shore A at the test slab

revision index
3

revision date
9/9/2016

page 3 / 3

No ASTM D2000 properties available

Specific characteristic and limitations for the use in food contact are set out in the corresponding declaration of conformities.

The material meets the requirements of USP Class VI -121°C.

The given values are based on a limited number of tests on standard test pieces (2mm sheets). The data from finished parts can deviate from above values depending on the manufacturing process and the component geometry.

The data represents our present empirical values. It is incumbent on the person placing the order to examine whether it is suitable for its intended purpose, before using the product. All questions regarding the guarantee of this product are in line with our terms and conditions, inasmuch as statutory provisions do not plan for something else.

Freudenberg

Freudenberg Sealing Technologies
Global Material Technology
Wolfgang Becker

Telefon: +49 (0)6201/80-2893
Fax: +49 (0)6201/88-2893
Email: wolfgang.becker@FST.com

