

Milling cutter holder (Weldon) with flat face

ISO 7388-1

ATORN[®]

Application

For clamping tools with lateral driving surfaces in accordance with DIN 1835 B and DIN 6535 HB

Version

- Pre-balanced G6.3/25,000 rpm
- Precision design
- Polished external and internal cones
- High concentricity

Advantage

- Increased rigidity and vibration damping due to positive-locking flat face
- Extends the service life of cutting tools



Art. No.	23157 553
Tool holding device	SK 40
Clamping diameter	12 mm
Projecting length	50 mm
Outer diameter	42 mm
Coolant supply	Yes
Balancing quality	G 6,3 at 25000 rpm
Concentricity tolerance	5 µm

EAN-Code

4050293647365