


MIRO 6.2 24VDC 250VAC/DC-1A OPTO-COUPLER MODULE



IN: 53 VDC - OUT: 250 VAC / 350 VDC / 1 A

Transistor 1 A
24 V DC
Screw terminals
Multi voltage output

[Link to Product](#)

Illustration





Product may differ from Image

Input

| | |
|-------------------|--------------|
| Voltage range ON | 10...53 V DC |
| Voltage range OFF | 0...5 V DC |
| Control current | 10 mA |
| LED display | LED (yellow) |

General data

| | |
|------------------------|--------------------------------|
| Test isolation voltage | 2.75 kV |
| Mounting method | DIN-rail mountable (EN 60715) |
| Housing | Black plastic, flame retardant |
| Temperature range | -20...+60 °C |
| Dimensions H × W × D | 90×6.2×65 mm |

Output

| | |
|------------------------------------|---------------------------|
| Switching time ON/OFF | 3/6 ms |
| Switching voltage | 5...250 V AC/5...350 V DC |
| Switching current per output | 1 mA...1 A |
| Saturation voltage (across output) | max. 0.7 V AC/DC |
| Leakage current (output is open) | max. 25 µA |

Switching frequency max. 10 Hz

Commercial data

country of origin CZ

customs tariff number 85414090

minimum order quantity 1