

Switch disconnecter 3LD3, main switch 3-polig, lu 16A operational switch at AC-23 A at 400 V 7,5 kW front mounted Base mounting with center-hole 22,5 mm rotary operationg mechanism black 66 x66 mm



Model	
Product brand name	SENTRON
Product designation	3LD Switch disconnecter
Design of the product	Main switch
Display version / for switch position indicator manual operation	1 ON - 0 OFF
Design of the operating mechanism	Short rotary knob
Design of handle	rotary operating mechanism, black
Type of the driving mechanism / motor drive	No
General technical data	
Number of poles	3
Type of device	fixed mounting
Type of switch	front mounted
Operating frequency / maximum	50 1/h
Voltage	
Insulation voltage / rated value	690 V
Surge voltage resistance / rated value	6 kV
Protection class	

Protection class IP	IP65	
Protection class IP / on the front	IP65	
Dissipation		
Power loss [W]	0.5 W	
<ul style="list-style-type: none"> • for rated value of the current / at AC / in hot operating state / per pole 		
Electricity		
Current / at AC / rated value	16 A	
Continuous current / rated value	16 A	
Short-time current resistance (I _{cw}) / at 690 V / limited to 1 s / rated value	500 A	
Main circuit		
Operating frequency	50 Hz	
<ul style="list-style-type: none"> • initial value 		
<ul style="list-style-type: none"> • Full-scale value 	60 Hz	
Operating power	7.5 kW	
<ul style="list-style-type: none"> • at AC-23 A / at 400 V / rated value 		
<ul style="list-style-type: none"> • at AC-23 A / at 690 V / rated value 		7.5 kW
<ul style="list-style-type: none"> • at AC-3 / at 400 V / rated value 		5.5 kW
<ul style="list-style-type: none"> • at AC-3 / at 690 V / rated value 	5.5 kW	
Operating voltage	690 V	
<ul style="list-style-type: none"> • at AC / at 50/60 Hz / rated value 		
Auxiliary circuit		
Operating voltage / of auxiliary contacts / at AC / maximum	500 V	
Continuous current / of the auxiliary contact / rated value	10 A	
Insulation voltage / of the auxiliary switch / rated value	500 V	
Suitability		
Suitability for use	Yes	
<ul style="list-style-type: none"> • Main switch 		
<ul style="list-style-type: none"> • switch disconnecter 		Yes
<ul style="list-style-type: none"> • EMERGENCY OFF switch 		Yes
<ul style="list-style-type: none"> • safety switch 		Yes
<ul style="list-style-type: none"> • maintenance/repair switch 		Yes
Product details		
Product feature / interlock	Yes	
Product extension / optional	No	
<ul style="list-style-type: none"> • motor drive 		
<ul style="list-style-type: none"> • Voltage trigger 		

Short-time current resistance (I _{cw}) / limited to 1 s / rated value	500 kA
Number of NC contacts	0
Number of NO contacts	0

Connections

Type of electrical connection	Box terminal
<ul style="list-style-type: none"> for main current circuit 	

Requirements

Design of the fuse link	
<ul style="list-style-type: none"> for short-circuit protection of the main circuit / required 	fuse gL/gG: 20 A
<ul style="list-style-type: none"> for short-circuit protection of the auxiliary switch / required 	fuse gL/gG: 10 A

Mechanical Design

Height	60 mm
Width	36 mm
Depth	114 mm
Mounting type	Built-in unit fixed-mounted version
Mounting type	
<ul style="list-style-type: none"> front mounting with 4-hole attachment 	No
<ul style="list-style-type: none"> front mounting with central attachment 	Yes
<ul style="list-style-type: none"> rail mounting 	No
Net weight	200 g

Environmental conditions

Ambient temperature	
<ul style="list-style-type: none"> during operation / minimum 	-25 °C
<ul style="list-style-type: none"> during operation / maximum 	55 °C

Certificates

Equipment marking	
<ul style="list-style-type: none"> acc. to DIN EN 61346-2 	S
<ul style="list-style-type: none"> acc. to DIN EN 81346-2 	SF

Declaration of Conformity



Further information

Information- and Downloadcenter (Catalogs, Brochures,...)
<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3LD3054-0TK51>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3LD3054-0TK51>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3LD3054-0TK51

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



