


MIRO TH 24VDC SK 5P OPTO-COUPLER MODULE



IN: 53 VDC - OUT: 250 VAC / 0,5A

Triac 0.5 A
24 V DC
with auxiliary common contacts
Screw terminals

[Link to Product](#)

Illustration





Product may differ from Image

Approvals



Input

| | |
|-------------------|--------------|
| Voltage range ON | 10...44 V DC |
| Voltage range OFF | 0...3 V DC |
| Control current | 6 mA |
| LED display | LED (yellow) |

General data

| | |
|------------------------|--------------------------------|
| Test isolation voltage | 2.5 kV |
| Mounting method | DIN-rail mountable (EN 60715) |
| Housing | Black plastic, flame retardant |
| Temperature range | -20...+60 °C |
| Dimensions H × W × D | 78×6.2×65 mm |

Output

The information in this brochure has been compiled with the utmost care.

Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 05/15

| | |
|------------------------------------|--------------------------------------|
| Switching voltage | 12...250 V AC |
| Switching current per output | 1 mA...0.5 A |
| Saturation voltage (across output) | max. 1.5 V AC |
| Leakage current (output is open) | max. 0.3 mA |
| Switching time ON/OFF | 10/10 ms |
| Switching frequency | max. 20 Hz, depending on suppression |

Commercial data

| | |
|------------------------|----------|
| country of origin | CZ |
| customs tariff number | 85414090 |
| minimum order quantity | 1 |