




## Measuring leads

### PL 2600 S W



Product	PL 2600 S W
description	Safety test lead with dual function safety test probe. Tip for penetration of oxide layers and 4 mm diameter pin for insertion into sockets. 4 mm diameter safety connector with right-angled outlet. Incl.
operating instruction	BA452
article-no. / *colour	9341581xx <div style="display: flex; justify-content: space-around; align-items: center;"> <div style="text-align: center;">  00 black         </div> <div style="text-align: center;">  01 red         </div> </div>
<b>Ni</b>	
drawing	
technical data	
rated voltage <sup>(1)</sup>	AC/DC 1000 V
measurement cat. acc. to IEC 61010	CAT II
rated current <sup>(1)</sup> (consider derating curve)	16 A
material plug	brass, nickel plated
housing material	PA, PP
temperature range acc. To IEC61010 <sup>(2)</sup>	-15 °C to +70 °C
inflammability class acc. to UL 94 (only valid for basic material of housing)	HB
cable length	100 cm
conductor size	1 mm <sup>2</sup>

4 mm safety system

cable material	PVC
contact resistance	20 mOhm
standard	IEC 61010

<sup>(1)</sup> for normal environmental conditions -5°C to +40°C

<sup>(2)</sup> contact the manufacturer for applications at deviating temperature ranges

stand: 23.07.2018