

PROFESSIONAL CAST IRON CLAMP

Description

Power up to 12,000 N. Safety matting at the end of the rail. Treated steel brake included in the slide for blocking. Cold-drawn steel Rail. Valve and slide in high-strength GS cast iron, epoxy protected. With protective clamping jaws.

Strong points

20 machining and control operations during fabrication Power up to 12000 N



Characteristics

Ref.	EAN	Clamping mm	Projection mm	Rail mm
611171	3660338007484	200	80	30x8
611172	3660338007491	300	80	30x8
611173	3660338007507	400	80	30x8
611174	3660338007514	500	80	30x8
611175	3660338007521	600	80	30x8
611176	3660338007538	800	80	30x8
652543	3660338007545	300	100	35X9
652544	3660338007552	400	100	35X9
652545	3660338007569	500	100	35X9
652546	3660338007576	600	100	35X9
652547	3660338007583	800	100	35X9
652548	3660338007590	1000	100	35X9
652549	3660338007606	1500	100	35X9
652550	3660338007613	2000	100	35X9
652551	3660338007620	400	150	40x9
652552	3660338007637	600	150	40x9
652553	3660338007644	800	150	40x9
652554	3660338007651	1000	150	40x9
652555	3660338007668	1500	150	40x9
652556	3660338007675	2000	150	40x9