

COMPONENT SPECIFICATION

Name	Ferrite Chip EMI Suppressors MLB321611-0090PQ	COMPOSITE SPECIFICATION		1 / 2
		SPEC#	MLB321611-0090PQ	

1. SCOPE

This specification applies to the MLB-3216 series Ferrite Chip EMI suppressors.

2. STANDARD ATMOSPHERIC CONDITIONS

Unless otherwise specified the standard range of atmospheric conditions for making measurements and tests is as follows:

Ambient temperature : $20 \pm 15^\circ\text{C}$

Relative humidity : 30~70%

If there may be any doubt on the results, measurements shall be made within the following limits :

Ambient temperature : $25 \pm 5^\circ\text{C}$


Relative humidity : 30~70%

3. RATINGS

IMPEDANCE (Ω) AT100 MHz 500mV	DC RESISTANCE (Ω) Max	※ RATED CURRENT (mA) Max
$90 \pm 25\%$	0.04	3000

※The maximum rated current : the DC current value having temperature increased 40°C after thru DC current 2 hours at ambient temperature.

4. DIMENSION



OPERATING TEMP. RANGE : $-55^\circ\text{C} \sim +125^\circ\text{C}$

STORAGE TEMP. RANGE : $-10^\circ\text{C} \sim +40^\circ\text{C}$

L	W	T	A
3.2 ± 0.2	1.6 ± 0.2	1.1 ± 0.2	0.4~1
<small>(0.126±0.008)</small>	<small>(0.063±0.008)</small>	<small>(0.043±0.008)</small>	<small>(0.016~0.039)</small>

HISTORY	DATE	REVISION	SIGN.	SIGN.
PLANNED BY	CHECKED BY	APPROVED BY		

COMPONENT SPECIFICATION

Name	Ferrite Chip EMI Suppressors	COMPOSITE SPECIFICATION		2 / 2
	MLB321611-0090PQ	SPEC#	MLB321611-0090PQ	

