


High Intensity LED, Ø 5 mm Untinted Non-Diffused Package



www.vishay.com

DESCRIPTION

The TLH.51.. series is a clear, non diffused 5 mm LED for outdoor application.

These clear lamps utilize the highly developed technologies like AllnGaP and GaP.

The lens and the viewing angle is optimized to achieve best performance of light output and visibility.

FEATURES

- Untinted non-diffused lens
- Choice of three colors
- TLH.5100 for cost effective design
- Medium viewing angle
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912

APPLICATIONS

- Outdoor LED panels
- Central high mounted stop lights (CHMSL) for motor vehicles
- · Instrumentation and front panel indicators
- Light guide design
- Traffic signals

PRODUCT GROUP AND PACKAGE DATA

- Product group: LED
- Package: 5 mm
- Product series: standard
- Angle of half intensity: ± 9°

PARTS TABLE															
PART	LUMINOUS COLOR (m		OUS INT (mcd)	140		• • • • • • • • • • • • • • • • • • • •		at I _F (mA)	FORWARD VOLTAGE (V)		at I _F (mA)	TECHNOLOGY			
		MIN.	TYP.	MAX.	(111,4)	MIN.	TYP.	MAX.		MIN.	TYP.	MAX.		(IIIA)	
TLHK5100	Red	320	1400	-	20	626	630	639	10	-	2	2.6	20	AllnGaP on GaAs	
TLHK5100-AS12Z	Red	320	1400	-	20	626	630	639	10	-	2	2.6	20	AllnGaP on GaAs	
TLHE5100	Yellow	750	1800	-	20	581	588	594	10	-	2	2.6	20	AllnGaP on GaAs	
TLHG5100	Green	240	450	-	20	562	-	575	10	-	2.4	3	20	GaP on GaP	

ABSOLUTE MAXIMUM RATINGS (T _{amb} = 25 °C, unless otherwise specified)	
TLHK510., TLHE510., TLHG510.	

PARAMETER	TEST CONDITION	SYMBOL	VALUE	UNIT
Reverse voltage		V _R	6	V
DC forward current	T _{amb} ≤ 65 °C	I _F	30	mA
Surge forward current	t _p ≤ 10 μs	I _{FSM}	1	A
Power dissipation	T _{amb} ≤ 65 °C	Pv	100	mW
Junction temperature		Tj	100	°C
Operating temperature range		T _{amb}	-40 to +100	°C
Storage temperature range		T _{stg}	-55 to +100	°C
Soldering temperature	$t \le 5$ s, 2 mm from body	T _{sd}	260	°C
Thermal resistance junction/ambient		R _{thJA}	350	K/W





RoHS

COMPLIANT

HALOGEN

FREE

1





www.vishay.com

Vishay Semiconductors

OPTICAL AND ELECTRICAL CHARACTERISTICS ($T_{amb} = 25 \text{ °C}$, unless otherwise specified) TLHK510., RED							
PARAMETER	TEST CONDITION	SYMBOL	MIN.	TYP.	MAX.	UNIT	
Luminous intensity (1)	I _F = 20 mA	IV	320	1400	-	mcd	
Dominant wavelength	I _F = 10 mA	λ _d	626	630	639	nm	
Peak wavelength	I _F = 10 mA	λρ	-	643	-	nm	
Angle of half intensity	I _F = 10 mA	φ	-	± 9	-	deg	
Forward voltage	I _F = 20 mA	V _F	-	2	2.6	V	
Reverse voltage	I _R = 10 μA	V _R	5	-	-	V	
Junction capacitance	V _R = 0 V, f = 1 MHz	Cj	-	15	-	pF	

Note

 $^{(1)}~$ In one packing unit $I_{Vmin.}/I_{Vmax.} \leq 0.5$

OPTICAL AND ELECTRICAL CHARACTERISTICS ($T_{amb} = 25 \text{ °C}$, unless otherwise specified) TLHE510., YELLOW							
PARAMETER	TEST CONDITION	SYMBOL	MIN.	TYP.	MAX.	UNIT	
Luminous intensity ⁽¹⁾	I _F = 20 mA	Iv	750	1800	-	mcd	
Dominant wavelength	I _F = 10 mA	λ _d	581	588	594	nm	
Peak wavelength	I _F = 10 mA	λρ	-	590	-	nm	
Angle of half intensity	I _F = 10 mA	φ	-	± 9	-	deg	
Forward voltage	I _F = 20 mA	V _F	-	2	2.6	V	
Reverse voltage	I _R = 10 μA	V _R	5	-	-	V	
Junction capacitance	V _R = 0 V, f = 1 MHz	Cj	-	15	-	pF	

Note

 $^{(1)}$ In one packing unit $I_{Vmin.}/I_{Vmax.} \leq 0.5$

OPTICAL AND ELECTRICAL CHARACTERISTICS (T _{amb} = 25 °C, unless otherwise specified)
TLHG510., GREEN

•						
PARAMETER	TEST CONDITION	SYMBOL	MIN.	TYP.	MAX.	UNIT
Luminous intensity ⁽¹⁾	I _F = 20 mA	IV	240	450	-	mcd
Dominant wavelength	I _F = 10 mA	λ_d	562	-	575	nm
Peak wavelength	I _F = 10 mA	λp	-	565	-	nm
Angle of half intensity	I _F = 10 mA	φ	-	± 9	-	deg
Forward voltage	I _F = 20 mA	V _F	-	2.4	3	V
Reverse voltage	I _R = 10 μA	V _R	6	15	-	V
Junction capacitance	V _R = 0 V, f = 1 MHz	Cj	-	50	-	pF

Note

 $^{(1)}$ In one packing unit $I_{Vmin.}/I_{Vmax.} \leq 0.5$



TLHE510., TLHG510., TLHK510.

MAX.

584

586

588

590

592

594

· Wavelengths are tested at a current pulse duration of 25 ms.

DOM. WAVELENGTH (nm)

COLOR CLASSIFICATION

MIN.

581

583

585

587

589

591

GROUP

0

2

3

4

5

6

7

8

Note

YELLOW

Vishay Semiconductors

MIN.

562

564

566

568

570

572

GREEN

MAX.

565

567

569

571

573

575

LUMINOUS INTENSITY CLASSIFICATION								
GROUP	LIGHT INTENSITY (mcd)							
STANDARD	MIN.	MAX.						
Z	240	480						
AA	320	640						
BB	430	860						
CC	575	1150						
DD	750	1500						
EE	1000	2000						
FF	1350	2700						
GG	1800	3600						
НН	2400	4800						
II	3200	6400						
KK	4300	8600						

Note

 Luminous intensity is tested at a current pulse duration of 25 ms. The above type numbers represent the order groups which include only a few brightness groups. Only one group will be shipped on each bag (there will be no mixing of two groups on each bag).

In order to ensure availability, single brightness groups will not be orderable.

In a similar manner for colors where wavelength groups are measured and binned, single wavelength groups will be shipped in any one bag.

In order to ensure availability, single wavelength groups will not be orderable.

TYPICAL CHARACTERISTICS (T_{amb} = 25 °C, unless otherwise specified)




Fig. 1 - Forward Current vs. Ambient Temperature




Fig. 2 - Forward Current vs. Pulse Length



TLHE510., TLHG510., TLHK510.

Vishay Semiconductors




Fig. 3 - Relative Radiant Sensitivity vs. Angular Displacement




Fig. 4 - Forward Current vs. Forward Voltage




Fig. 5 - Relative Luminous Intensity vs. Ambient Temperature




Fig. 6 - Relative Luminous Intensity vs. Forward Current




Fig. 7 - Relative Intensity vs. Wavelength




Fig. 8 - Forward Current vs. Forward Voltage

4 For technical questions, contact: <u>LED@vishav.com</u>

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000






Fig. 9 - Relative Luminous Intensity vs. Ambient Temperature




Fig. 10 - Relative Luminous Intensity vs. Forward Current




Fig. 11 - Relative Intensity vs. Wavelength

Vishay Semiconductors




Fig. 12 - Forward Current vs. Forward Voltage




Fig. 13 - Relative Luminous Intensity vs. Ambient Temperature




Fig. 14 - Relative Luminous Intensity vs. Forward Current

5



TLHE510., TLHG510., TLHK510.

Vishay Semiconductors






Fig. 15 - Relative Intensity vs. Wavelength

PACKAGE DIMENSIONS in millimeters







R 2.49 (sphere)




according to DIN specifications

Rev. 2.5, 16-Mar-15

6

Document Number: 83010




Label 4 8667-2 Fig. 16 - Tape Direction

Note

The new nomenclature for ammopack is e.g. ASZ only, without suffix for the LED orientation. The carton box has to be turned to the desired
position: "+" for anode first, or "-" for cathode first. AS12Z and AS21Z are still valid for already existing types, BUT NOT FOR NEW DESIGN.

TAPE DIMENSIONS in millimeters



OPTION	DIMENSION "H" ± 0.5 mm	DIMENSION "X" ± 0.5 mm
AS	17.3	-

Rev. 2.5, 16-Mar-15

For technical questions, contact: <u>LED@vishay.com</u> THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT <u>www.vishay.com/doc?91000</u>



Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Material Category Policy

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.

Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as Halogen-Free follow Halogen-Free requirements as per JEDEC JS709A standards. Please note that some Vishay documentation may still make reference to the IEC 61249-2-21 definition. We confirm that all the products identified as being compliant to IEC 61249-2-21 conform to JEDEC JS709A standards.