

Screw tap, HSSE M ISO 2 (6H) 0° 371 B

For use in stainless steels

ATORN[®]



Application

For producing metric threads on CNC or conventional machines in **through holes** in the stainless steel material group.

Version

- With exposed teeth and reinforced shank

Advantage

- Innovative cutting geometry with exposed teeth reduces the torque, improves lubricant distribution and ensures very high process reliability and chip removal
- Specialised insert with optimised chipping geometry for use in stainless steels with adhesive or lubricating properties

Application	Steel (N/mm ²)			Stainless steel		Alu		Brass		Bronze		Plastics	Graphite G(C)FK	GG(G) GjMW	Titan-alloy	Nickel-alloy	Super-alloy	Hard mat.	
	<700	<1000	<1300	marten.	austen.	short	long	short	long	short	long							<55 HRC	<65 HRC
	16	11		9	10														

Art. No.	13088 100
Type	M MAX Control
Thread type	Metric thread
Thread type x nominal diameter	M10
Pitch	1.5 mm
Hole type	Clearance hole ≤ 3xD
Cutting material	HSSE
Surface	Uncoated
Lead angle shape	B
Tolerance of screw taps	ISO 2 (6H)
Twist angle	0°
Shaft diameter	10 mm
Application type/machine type	CNC, Conventional
Core hole diameter	8.5 mm
Coolant supply	External
Length	100 mm
Shank square	8 mm
Cutting speed (steel 1000) suitability	2
Cutting speed (steel 1300) suitability	3
Overall stainless steel suitability	1
fitness not iron total	3
fitness Titan/Nickel/Super total	3
Cutting speed (cast) suitability	3
Cutting speed (hard 55) suitability	3
Cutting speed (hard 65) suitability	3
DIN	371

EAN-Code

4050293016932