

## Circular metal saw blade, HSS, finely toothed, form A

For universal use up to 1000 N/mm<sup>2</sup> in thin-walled workpieces and shallow cutting depths, on conventional machines

**ORION**<sup>®</sup>

### Application:


For making saw cuts in thin-walled workpieces and shallow cutting depths in the material groups of steel, stainless steel, cast iron and non-ferrous metals.

### Execution:

- Precision-ground circular metal saw blade with tooth shape A, finely toothed, laterally hollow ground, hole without keyway, up to a diameter of 160 mm without collar, from a diameter of 200 mm with collar

### Advantage:

- Innovative cutting geometry ensures very high dimensional accuracy, process reliability and chip removal
- High-quality cutting material for very high service life requirements
- Universal use in numerous applications



<b>Art. no.</b>	<b>14002 170</b>
<b>Brand</b>	ORION
<b>Manufacturer Part Number</b>	14002170
<b>Tooth shape</b>	A
<b>Cutting material</b>	HSS
<b>Thickness of cutting edge</b>	0.6 mm
<b>Tolerance of cutting edge diameter</b>	js15
<b>Tolerance of cutting edge thickness</b>	js11
<b>Tolerance of hole diameter</b>	H7
<b>Cutting edge diameter</b>	20 mm
<b>Bore diameter</b>	5 mm
<b>Number of teeth</b>	48 PCS
<b>DIN</b>	1837
<b>Gross Weight</b>	0.001 kg
<b>Product Group</b>	1QK

### EAN

4039247078677