

## moveable power clamp

Long version



### Application:

For quick and secure clamping on machine tables and appliances.

### Execution:

- Use in T-grooves of 14-28 mm and on M12 and M16 grid plates.
- Sturdy clamping element made from alloyed tempered steel for variable clamping heights on movable basic element.
- Four different thrust-piece variants
- Continuously adjustable clamping element made of alloyed heat-treated steel in a forged, zinc-plated version.
- Pressure piece in smooth and grooved versions available as option.

### Advantage:

- low design height
- clamping force up to 30 kN or 43 kN
- continuously adjustable height and length
- for use in T-grooves 14-24 mm or grid plates M12 and M16
- 2 pressure piece variants



<b>Art. no.</b>	<b>26242 343</b>
<b>Brand</b>	AMF
<b>Manufacturer Part Number</b>	556188
<b>Tension force</b>	43
<b>Thread dimension</b>	M16
<b>Groove width</b>	18 mm
<b>Min./max. clamping height</b>	5-80 mm
<b>Min./max. boom arm length</b>	16-134 mm
<b>Height</b>	42 mm
<b>Height 2</b>	105 mm
<b>Length 3</b>	32 mm
<b>Width</b>	60 mm
<b>Thickness</b>	20 mm
<b>Thread dimension 2</b>	M20
<b>Length</b>	155 mm
<b>Length 2</b>	16 mm
<b>Width across flats</b>	10 mm
<b>Gross Weight</b>	3.352 kg
<b>Product Group</b>	260

### EAN

4020772553333