

Pneumatic impact screwdriver RR-160 H

Tightening torque 580 Nm



Application:

For heavy screw-driving work.

Execution:

- 3 power levels in clockwise rotation, 1 power level in anti-clockwise rotation

Delivery:

In cardboard box



Art. no.	75066 004
Brand	RED ROOSTER
Manufacturer Part Number	RR-160H
Model	RR-160 H
Suitable for screw	M10
Max. tightening torque	580 Nm
Max. idle speed	8000 rpm
Air consumption	252 l/min
Tool holding device	1/2-inch external square
Hammer mechanism system	Dynapact hammer mechanism
Length	185 mm
Connection thread	3/8 inch
Inner hose diameter	10 mm
Operating pressure	6.3 bar
Weight	2.3 kg
With right/left-hand rotation	Yes
Gross Weight	2.762 kg
Product Group	7AE

EAN

8717981000272