



DATA SHEET	0152017
DIN compensating cable KN 12 L 2x1,5 oval	valid from : 01.12.2008

Application

The compensating cable KN 12 L 2 x 1,5 mm² is a PVC insulated cable which transmits the thermoelectric voltage of NiCr/Ni thermocouples. It is for flexible use and fixed installation in dry and damp rooms. They may only be installed outdoors with UV protection and in observation of the max. permitted temperature range.

Design

Conductor	1,5 mm ² (48 x 0,20 mm)
Conductor material	KCA alloying, accuracy class 2 according DIN 43722 Positive conductor: Fe (iron) Negative conductor: CuNi (cupronickel)
Core insulation	PVC compound
Core identification	Positive conductor: red Negative conductor: green
Core layering	Cores parallel next to each other
Outer sheath	PVC compound, colour: green

Electrical properties

Limiting deviation class 2 ± 100 µV (± 2,5 °C) / m measuring point temperature +900 °C

Mechanical and thermal properties

Temperature range	occasional flexing: -5 °C up to +70 °C
Minimum bending radius	occasional flexing: 12 x cable diameter
Flammability	flame retardant in acc. to IEC 60332-1-2 resp. VDE 0482-332-1-2

Originator: Frank Hörtnagl / PD-KL Approved: Werner Körner / TE	Document: DB0152017EN	page 1 of 1
--	----------------------------	-------------