

U.I. Lapp GmbH	<b>DATASHEET</b>	
	<b>SKINDICHT® SR-SV</b>	52023628 14.11.2013

For high temperatures  
Resistant to oils, solvents, acids and chemicals  
Seawater-resistant  
High strain relief  
Robust



Good chemical resistance



Optimum strain relief



Robust



Temperature-resistant

### Application range

Special cable gland with VITON® anti-kink sleeve. Our own reinforced acid-resistant VITON® receptacle does not show any effects of aging even after an extended period of use at a temperature of +165°C.

Machine and turbine manufacturing  
Power plant engineering  
Laboratory

### Design

PG connection thread

### Note

Counter nut to be used: SKINDICHT® SM  
EMC version is available upon request

### Remark

Viton® is a registered trademark of DuPont de Nemours  
Photographs are not to scale and do not represent detailed images of the respective products.

Product Management	Document: SKINDICHT® SR-SV	1 / 3
--------------------	----------------------------	-------


U.I. Lapp GmbH	<b>DATASHEET</b>	 <b>LAPP GROUP</b>
	<b>SKINDICHT® SR-SV</b>	<b>52023628</b> <b>14.11.2013</b>

### Technical Data

Article designation / size:	SR-SV 21/17
Clamping range ØF (mm):	15 - 17
Max. fitting size for installation (mm):	46
SW1/SW2 mm:	30 / 30
Overall length, C (mm):	79
Thread length, D (mm):	7
Pieces / PU:	10
Caution:	The installation dimensions can be found in appendix T21
On request:	Available with long connection thread
Material:	Body: nickel-plated brass O-ring: FKM Anti-kink protection: FKM
Protection rating:	IP 65
Temperature range:	-15°C to +165°C

Product Management	Document: SKINDICHT® SR-SV	2 / 3
--------------------	----------------------------	-------

U.I. Lapp GmbH	<h1>DATASHEET</h1>	 <b>LAPP GROUP</b>
	<b>SKINDICHT® SR-SV</b>	52023628 14.11.2013



Product Management	Document: SKINDICHT® SR-SV	3 / 3
--------------------	----------------------------	-------