



EcoLED T8

T8 ECOLED STD 1200MM G1318W840

This T8 tube is the ideal product for quickly and economically converting fluorescent tube luminaires to the new LED technology. With a small technical intervention you will thus have extremely energy-saving luminaires.

Order code 56232

EAN 8002219736505

Technical specifications

Absorbed Power	18 W
Lampholder	G13
Supply voltage type	AC
Nominal voltage (AC)	230 Vac
Ambient temperature (min)	-20 °C
Ambient temperature (max)	40 °C
CCT light tone	4000 K
Photobiological risk	RG0
Beam angle	180 °
Bulb shape	Other
Colour consistency	SDCM6
Consumption (1000h)	18 KWh
CRI color rendering	>80
Diameter	28 mm
Efficiency	105 lm/W
Energy class	F
Eprel code	562927
Equivalent power	36W
Frequency (max)	60 Hz
Frequency (min)	50 Hz
Power factor	0.51
Life	15000 h
Lighting Sources Flux	1900 lm
Luminous flux L70B50	15000 h
Switching cycles	8000
Voltage supply range (max)	240 V
Voltage supply range (min)	220 V

Mechanical specifications

Height	1212 mm
Diffuser finiture	Frosted
Protection grade IP	IP20

Certifications and norms

UK SI 2021 No. 1095, EN IEC 55015:2019 + A11:2020, EN IEC 61000-3-2 :2019, EN 61547:2009, EN 62471:2008, EN 62776:2015, EN IEC 63000:2018, EN 62493:2010, EN 61000-3-3:2013, REG. 2019/2020(EU)

