

## Product information

# 64 32 120

## Electronics End Cutting Nipper

DIN ISO 9654



- Precision pliers for ultra fine cutting work, e. g. in electronics and fine mechanics
- Sturdy, zero backlash box joint
- Low-friction double spring for gentle and even opening
- The polish or mirror polish together with a fine film of oil offer effective rust protection - no circuit faults caused by peeling chrome from plated tools
- Cutters additionally laser hardened, cutter hardness at least 56 HRC
- Oblique End Cutter, short head, with small bevel,  $\alpha = 15^\circ$
- Ball bearing chrome steel, oil hardened

MM   $\angle 15^\circ$

### General

|                 |                            |
|-----------------|----------------------------|
| Article No.     | 64 32 120                  |
| EAN             | 4003773017820              |
| Head            | mirror polished            |
| Handles         | with multi-component grips |
| Weight          | 70 g                       |
| Dimensions      | 120 x 67 x 17 mm           |
| Standard        | DIN ISO 9654               |
| REACH compliant | does not contain SVHC      |
| RoHS compliant  | not applicable             |

### Technical details

|                                                |          |
|------------------------------------------------|----------|
| Cutting capacities soft wire (diameter)        | Ø 1.5 mm |
| Cutting capacities medium hard wire (diameter) | Ø 1.0 mm |
| Cutting capacities hard wire (diameter)        | Ø 0.5 mm |
| Head width (A)                                 | 11 mm    |
| Jaw length (B)                                 | 10 mm    |
| Jaw thickness (joint) (D)                      | 7 mm     |
| Cutting edge length mm (C)                     | 17 mm    |

*technical change and errors excepted*

