

SCSC clamping holder, positive, right

For longitudinal turning with CC indexable insert

ATORN[®]

Application


For longitudinal turning with CC indexable insert, 80°

Version

- precision-manufactured steel carrier, bronzed, hardened, type S, attack angle 45°, tip angle 90°, clearance angle 7°

Advantage

- Robust geometry for longitudinal turning
- positive body geometry ensures low cutting forces



Art. no.	17830 844
ISO name	SCSC R/L 2525 M12
Shaft height	25 mm
Shank width	25 mm
Length	150 mm
Length of head	27 mm
Programming size	32 mm
Suitable for indexable inserts	CC.. 1204..
Tool design	Right

EAN-Code

4050293562927