

## Revolving centring point

Slim; with extended moving point, 60°/30°



### Application:

For mounting and supporting long and projecting lathe parts with centre drill hole to avoid imbalance and to encourage stabilisation.

### Execution:

- With extended moving point 60°/30°.
- Body and moving point are hardened and ground.

### Advantage:

- Particularly favourable where conditions on the lathe are confined.
- Precision roller bearings ensure a high level of concentricity.

### Delivery:

1x revolving centring point.



|                                     |                  |
|-------------------------------------|------------------|
| <b>Art. no.</b>                     | <b>22133 050</b> |
| <b>Brand</b>                        | RÖHM             |
| <b>Manufacturer Part Number</b>     | 362083           |
| <b>Morse taper size</b>             | MK 5             |
| <b>Programming size</b>             | 119 mm           |
| <b>Programming size for housing</b> | 70 mm            |
| <b>Max. workpiece weight</b>        | 1400 kg          |
| <b>Max. rotation speed</b>          | 4300 rpm         |
| <b>Concentricity tolerance</b>      | 0.01 mm          |
| <b>Diameter of housing</b>          | 58 mm            |
| <b>Tip diameter</b>                 | 30 mm            |
| <b>Gross Weight</b>                 | 3.060 kg         |
| <b>Product Group</b>                | 201              |

### EAN

401920809444 1