




HF3 Relay

- Y-Design
- **■** Frequency range DC to 3GHz
- Impedance 50Ω or 75Ω
- Small dimensions (14.6x7.2x10mm)
- 1 form C contact (1 changeover contact)
- **■** Immersion cleanable
- Low power consumption (≤140mW)

Typical applications

Cable modems and linecards/ CATV, Tabs, measurement and test equipment ATE, satellite / audio / video tuners, wireless base stations and antennas, switching boards



Coil Data	
Coil voltage range	3 to 24VDC

Coil	vareione	monostable	

Coil Rated Operate Limiting Release Co	il Rated coil
code voltage voltage voltage resista	ance power
VDC VDC VDC VDC $\Omega\pm10$	0% mW
50Ω version, monostable, 1 coil	
51 3 2.25 6.50 0.30 64	140
52 4.5 3.38 9.80 0.45 148	5 140
53 5 3.75 10.90 0.50 178	3 140
54 6 4.50 13.00 0.60 25	7 140
55 9 6.75 19.60 0.90 574	4 140
56 12 9.00 26.10 1.20 102	28 140
57 24 18.00 52.30 2.40 411	4 140
75Ω version, monostable, 1 coil	
01 3 2.25 6.50 0.30 64	140
02 4.5 3.38 9.80 0.45 148	5 140
03 5 3.75 10.90 0.50 178	3 140
04 6 4.50 13.00 0.60 25	7 140
05 9 6.75 19.60 0.90 574	4 140
06 12 9.00 26.10 1.20 102	28 140
07 24 18.00 52.30 2.40 411	4 140

All figures are given for coil without pre-energization, at ambient temperature +23°C.



Coil Data (continued)

Coil ver	rsions, bist	able				
Coil	Rated	Set	Limiting	Reset	Coil	Rated coil
code	voltage	voltage	voltage	voltage	resistance	power
	VDC	VDC	VDC	VDC	Ω±10%	mW
50Ω vei	rsion, bista	ble, 1 coil				
71	3	2.25	9.20	-2.25	128	70
72	4.5	3.38	13.85	-3.38	289	70
73	5	3.75	15.30	-3.75	357	70
74	6	4.50	18.50	-4.50	514	70
75	9	6.75	27.70	-6.75	1157	70
76	12	9.00	37.00	-9.00	2057	70
77	24	18.00	74.00	-18.00	8228	70
50Ω ver	rsion, bista	ble, 2 coils	3			
91	3	2.25	6.50	2.25	64	140
92	4.5	3.38	9.80	3.38	145	140
93	5	3.75	10.90	3.75	178	140
94	6	4.50	13.00	4.50	257	140
95	9	6.75	19.60	6.75	574	140
96	12	9.00	26.10	9.00	1028	140
97	24	18.00	52.30	18.00	4114	140

All figures are given for coil without pre-energization, at ambient temperature +23°C.

Coil Data (continued)

Coil ver	sions, bist	able				
Coil	Rated	Set	Limiting	Reset	Coil	Rated coil
code	voltage	voltage	voltage	voltage	resistance	power
	VDC	VDC	VDC	VDC	Ω±10%	mW
75Ω ver	rsion, bista	ble, 1 coil				
21	3	2.25	9.20	-2.25	128	70
22	4.5	3.38	13.85	-3.38	289	70
23	5	3.75	15.30	-3.75	357	70
24	6	4.50	18.50	-4.50	514	70
25	9	6.75	27.70	-6.75	1157	70
26	12	9.00	37.00	-9.00	2057	70
27	24	18.00	74.00	-18.00	8228	70
75Ω ver	sion, bista	ble, 2 coils	3			
41	3	2.25	6.50	2.25	64	140
42	4.5	3.38	9.80	3.38	145	140
43	5	3.75	10.90	3.75	178	140
44	6	4.50	13.00	4.50	257	140
45	9	6.75	19.60	6.75	574	140
46	12	9.00	26.10	9.00	1028	140
47	24	18.00	52.30	18.00	4114	140


All figures are given for coil without pre-energization, at ambient temperature +23°C.






HF3 Relay (Continued)

Coil operating Range





Insulation Data	50Ω version	75Ω version
Initial dielectric strength		
between open contacts	600	V_{rms}
between contact and coil	1000	OV _{rms}
Initial surge withstand voltage		
between open contacts	100	VOC
between contact and coil	150	VOC

RF Data		
Isolation		
at 100MHz/900MHz	80dB/72dB	80dB/72dB
at 3GHz	45dB	40dB
Insertion loss		
at 100MHz/900MHz	0.03dB/0.12dB	0.03dB/0.12dB
at 3GHz	0.35dB	0.40dB
Voltage standing wave ratio (VSWR)	
at 100MHz/900MHz/3GHz	1.05/1.20/1.20	1.05/1.20/1.40

Other E	Data
---------	------

Material compliance: EU RoHS/ELV, China RoHS, REACH, Halogen content refer to the Product Compliance Support Center at www.te.com/customersupport/rohssupportcenter

Ambient temperature -55°C to +85°C Thermal resistance <165K/W

Category of environmental protection

IEC 61810 RT III - wash tight
Degree of protection, IEC 60529 IP 67, immersion cleanable
Vibration resistance (functional) 35g, 10 to 1000Hz
Shock resistance (functional), half sinus 11ms 50g

Shock resistance (destructive), half sinus 0.5ms 150g
Terminal type SMT
Weight max. 2.5g

Resistance to soldering heat SMT

IEC 60068-2-58 265°C/10s Moisture sensitive level, JEDEC J-Std-020D MSL3 Ultrasonic cleaning not recommended


Packaging/unit reel/400 pcs., box/400 or 2000 pcs.




RELAY PRODUCTS

HF3 Relay (Continued)


Typical RF performance, 50Ω version




Typical RF performance, 75Ω version





Typical RF performance, 50Ω version (continued)



Typical RF performance, 75Ω version (continued)








Bistable, 2 coils


Terminal assignment

TOP view on component side of PCB





Bistable, 1 coil






HF3 Relay (Continued)


PCB layout

TOP view on component side of PCB

50Ω version



75Ω version





Dimensions

50Ω version




 $C\,o\,p\,I\,a\,n\,a\,r\,\,i\,\,f\,y \leq 0\,,\,1\,0\,mm$







75Ω version



Coplanarity ≤ 0 .10mm










HF3 Relay (Continued)


Processing




Packing







Resistance to soldering heat





AXICOM



HF3 Relay (Continued)

Product code structure

Typical product code HF3 53

Гуре

HF3 Signal Relays HF3 Series

1 form C, 1 CO

Coil

Coil code: please refer to coil versions table

Performance type

5x 50Ω version, monostable 1coil0x 75Ω version, monostable 1coil7x 50Ω version, bistable 1coil2x 75Ω version, bistable 1coil9x 50Ω version, bistable 2coils4x 75Ω version, bistable 2coils

Product code	Arrangement	Version	Coil	Coil type	Part number
HF3 51	1 form C (1 CO)	50ohm	3VDC	Monostable	1462051-1
HF3 52			4.5VDC		1-1462051-6
HF3 53			5VDC		1462051-2
HF3 54			6VDC		1-1462051-7
HF3 55			9VDC		1462051-3
HF3 56			12VDC		1462051-4
HF3 57			24VDC		1462051-5
HF3 71	1 form C (1 CO)	50ohm	3VDC	Bistable 1 coil	1462051-6
HF3 72			4.5VDC		1-1462051-8
HF3 73			5VDC		1462051-7
HF3 76			12VDC		1462051-9
HF3 91	1 form C (1 CO)	50ohm	3VDC	Bistable 2 coils	1-1462051-1
HF3 92			4.5VDC		2-1462051-0
HF3 93			5VDC		1-1462051-2
HF3 95			9VDC		1-1462051-3
HF3 96			12VDC		1-1462051-4
HF3 97			24VDC		1-1462051-5
HF3 01	1 form C (1 CO)	75ohm	3VDC	Monostable	1462050-1
HF3 02			4.5VDC		1-1462050-6
HF3 03			5VDC		1462050-2
HF3 06			12VDC		1462050-4
HF3 07			24VDC		1462050-5
HF3 21	1 form C (1 CO)	75ohm	3VDC	Bistable 1 coil	1462050-6
HF3 23			5VDC		1462050-7
HF3 26			12VDC		1462050-9
HF3 41	1 form C (1 CO)	75ohm	3VDC	Bistable 2 coils	1-1462050-1
HF3 43			5VDC		1-1462050-2
HF3 46			12VDC		1-1462050-4
HF3 47			24VDC		1-1462050-5

This list represents the most common types and does not show all variants covered by this data sheet. Other types on request