HellermannTyton

MB3A10C2

Article Number: 151-28718

Adhesive Bases, .14" Max tie width, .75" Length/Width, .12" Hole Dia., PA66, White, 100/pkg



RoHS



Base Data

Local Order Number	MB3A10C2
Туре	MB3A
Color	White (WH)
Features and Benefits	 For use with 18 and 30 pound cable ties to provide stability when securing bundles. Secures with acrylic based adhesive backing for heavy bonding applications Can also be secured using two or four screws; providing multiple options. 4 way opening allows cable ties to be installed parallel or perpendicular to wire bundles.
Product Description	HellermannTyton adhesive fastened mounting bases are used with 18 through 150 pound cable ties to provide stability when securing bundles. The mounts are installed using the adhesive backing and/or by securing two or four screws. The 4 way opening allows the cable ties to be inserted parallel or perpendicular to the wire bundles.
Short Description	Adhesive Bases, .14" Max tie width, .75" Length/Width, .12" Hole Dia., PA66, White, 100/pkg

Product Dimensions

Length L (Imperial)	0.75 "		
Length L (Metric)	19.0 mm		
Fixation Method	Screw Mounting and Adhesive		
Width W (Imperial)	0.75 "		
Width W (Metric)	19.0 mm		
Cable Tie Width Max. (Imperial)	0.14 "		
Cable Tie Width Max. (Metric)	3.6 mm		
Height H (Imperial)	0.18 "		
Height H (Metric)	4.6 mm		
Mounting Hole Diameter D (Imperial)	0.12 "		
Mounting Hole Diameter D (Metric)	3.0 mm		
Mounting Hole Centers (Imperial)	0.52 "		
Thickness of Adhesive TA (Imperial)	0.031 "		
Mounting Hole Diameter D Max.			
(Metric) Mounting Hole Diameter D Min. (Metric)3.0 mm			
Thickness of Adhesive TA (Metric)			

Logistics and Packaging

Quantity Per	bag
Package Quantity (Metric)	100
Carton Quantity	10000

Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
Adhesive Shortcut	Synthetic rubber T50
Adhesive	Synthetic rubber with base of polyethylene foam
Adhesive Operating Temperature	-4°F to +122°F (-20°C to +50°C)
Flammability	UL94 V2 (excluding adhesive)
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
ROHS Compliant	Yes
UL Listed (US and Canada)	No
UL Recognized (US and Canada)	Yes

© HellermannTyton 2015