

Collet chuck extension

With internal cooling and straight shank

diebold

Application:

For clamping tools with a straight shank.

Execution:

- With straight shank, type ER standard.
- Particularly slim version for use in milling chucks as tool extension for deep machining operations where space is restricted.
- Wrench no. 23308 008 and collets 23320.
- Wrench no. 23308 008 and collets 23320.

Delivery:

1x collet chuck extension.



Art. no.	23304 130
Brand	DIEBOLD
Manufacturer Part Number	74.0.10.130
Collet type	ER 16
Shank diameter	12 mm
Min./max. clamping range	0.5-10 mm
Width across flats	25 mm
Outer diameter	28 mm
Shaft length	80 mm
Length of head	36 mm
Gross Weight	0.159 kg
Product Group	2AB