

Precision scales PCD



Application:

Ideal for working in glove bag or under laboratory extractors. Especially practical for weighing toxic, volatile or contaminated substances

Execution:

- Laboratory scales with separate platform
- PRE-TARE function for manual prior deduction of a known container weight, useful for fill level checks
- Freely programmable weighing unit, e.g. display directly in thread length g/m, paper weight g/m², or similar
- Level and foot screws for precise levelling of the scales come as standard, producing the most accurate weighing results
- high-resolution and flexible thanks to removable evaluation unit

Delivery:

with power supply unit and work protection hood



Art. no.	49000 014
Brand	KERN
Manufacturer Part Number	PCD 300-3
Type description	PCD 300-3
Max. weight measuring range	350 g
Digit increment, weight	0.001 g
Plate diameter	105 mm
Material of cover panel	Plastic
With unit counting	Yes
Min. item weight	20 mg
Reproducibility	0.002 g
Linearity	0.005 g
Settling time scale	4 s
Data transmission type	RS232
Housing dimensions (LxWxH)	165 x 280 x 75 mm
Display type	LCD
Gross Weight	2373.000 g
Product Group	447

EAN

4045761192034