


Data Sheet

Type Number 4276
Designation IEC LR 44
System Manganese Dioxide /
 Zinc / KOH - Electrolyte



Nominal Voltage 1,5 V
Typical Capacity C 125 mAh
 Load 5.6 kOhm, at 20°C down to 1.2 V

Weight (approx.) 1,8 g
Volume 0,51 ccm
Coding..... Manufacturing Month/Year by
 Letter Code

Temperature Ranges

	min	max.
Storage	-10°C	65 °C
Discharge	-10°C	65°C

Dimensions

	min	max.
Diameter	11,25	11,6
Height (A/B)	5	5,4

Segment Electronic

Main Applications Watch
 Photo
 Electronic

Typical Capacities (at 20°C)

Discharge Type	Load	End Voltage:	1.2 V
Continuous	5600 Ω	Time:	482 h
24h/d,7d/w		Capacity [mAh]:	125
Current [μA]:	270	Energy [MWh]:	168

All Data contained herein is for single cells

For battery applications, performance data may vary from single cell data, depending on specific battery configuration

VARTA Microbattery GmbH, Daimlerstr. 1, D-73479 Ellwangen/Jagst
 Tel.: (+49) 7961/921-0, Telefax: (+49) 7961/921-553

Subject to change without prior notice!
 Date of issue: 16.09.2003