

Wireless module - FL BT EPA 2

1005869

<https://www.phoenixcontact.com/pc/products/1005869>

Please be informed that the data shown in this PDF document is generated from our Online Catalog. Please find the complete data in the user documentation. Our General Terms of Use for Downloads are valid.



Bluetooth/Ethernet wireless module, 2.1+EDR/4.0, PAN P2P, internal antenna, IP65, 9 V DC ...
30 V DC, M12 connection, WEB, AT-commands and mode button

Your advantages

- Protocol-transparent communication on Layer 2
- Bluetooth wireless modul
- IP65 protection class
- Integrated antenna

Commercial Data

Item number	1005869
Packing unit	1 pc
Minimum order quantity	1 pc
Product Key	DNN2B1
Catalog Page	Page 375 (C-6-2019)
GTIN	4055626476087
Weight per Piece (including packing)	163.7 g
Weight per Piece (excluding packing)	105 g
Customs tariff number	85176200
Country of origin	SE

Technical Data

Product properties

Type	Stand-alone
Product type	Wireless module
Application	Ethernet

Wireless card

Number	1
Assembly instructions	Permanently installed

Electrical properties

Maximum power dissipation for nominal condition	1.7 W
---	-------

Supply: Module electronics

Connection technology	M12 connector
Connection method	M12 connector (A-coded, male)
Supply voltage	24 V DC
Supply voltage range	9 V DC ... 30 V DC
Supply current	typ. 36 mA (at 24 V DC)
Current consumption	max. 190 mA (at 9 V DC)

Input data

Digital

Number of inputs	1
------------------	---

Connection data

Power supply input

Connection method	M12 connector (A-coded, male)
-------------------	-------------------------------

Interfaces

Ethernet

Interface	Ethernet
Number	1
Connection method	M12 connectors (D-coded, female)

Functions

Configuration	Web interface, MODE button, AT commands (TCP/IP), SSC
Security	PIN
	Non-discoverable
Wireless licenses	Europe, USA, Canada, additional countries in the e-shop
	RED (Radio Equipment Directive)
	FCC 47 CFR part 15, subpart B
	Belgium

Wireless module - FL BT EPA 2



1005869

<https://www.phoenixcontact.com/pc/products/1005869>

Country support	Bulgaria
	Denmark
	Germany
	Estonia
	Finland
	France
	Greece
	Great Britain
	Ireland
	Iceland
	Italy
	Canada
	Croatia
	Latvia
	Liechtenstein
	Lithuania
	Luxembourg
	Malta
	Netherlands
	Norway
	Austria
	Poland
	Portugal
	Romania
	Sweden
	Switzerland
	Slovakia
	Slovenia
	Spain
	Czech Republic
Hungary	
USA	
Cyprus (rep.)	
Japan	
Cyprus (rep.)	

10/100 Mbps Ethernet

Number of interfaces	1
Connection method	M12 connectors (D-coded, female)
Note on the connection method	Auto negotiation and autocrossing
Transmission speed	10/100 Mbps
Transmission physics	Copper
Transmission length	100 m (per segment)

Wireless

Wireless module - FL BT EPA 2



1005869

<https://www.phoenixcontact.com/pc/products/1005869>

Designation	Bluetooth
Antenna connection method	(Internal)
Frequency range	2.402 GHz ... 2.48 GHz (Bluetooth)
Frequency band	2.4 GHz
Wireless standard	Bluetooth 2.1 + EDR
Transmission power	max. 10 dBm
Number of wireless interfaces	1 Bluetooth 2.1+EDR, Bluetooth LE 4.0
Wireless modules that can be connected	1
Profiles supported	PAN (NAP, PANU) GATT (central)

Dimensions

Width	67.8 mm
Height	92.7 mm
Depth	33.2 mm
Note on dimensions	Without M12 connections

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65
Ambient temperature (operation)	-40 °C ... 65 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Permissible humidity (operation)	5 % ... 93 % (non-condensing)
Permissible humidity (storage/transport)	non-condensing

EMC data

Electrostatic discharge

Standards/regulations	EN 61000-4-2
-----------------------	--------------

Electromagnetic HF field

Standards/regulations	EN 61000-4-3
-----------------------	--------------

Fast transients (burst)

Standards/regulations	EN 61000-4-4
-----------------------	--------------

Surge current load (surge)

Standards/regulations	EN 61000-4-5
-----------------------	--------------

Conducted interference

Standards/regulations	EN 61000-4-6
-----------------------	--------------

Emitted interference

Standards/regulations	EN 55022
-----------------------	----------

Mounting

Mounting type	Wall mounting
---------------	---------------

Wireless module - FL BT EPA 2

1005869

<https://www.phoenixcontact.com/pc/products/1005869>



Assembly instructions

Internal antenna

Wireless module - FL BT EPA 2



1005869

<https://www.phoenixcontact.com/pc/products/1005869>

Approvals



UL Listed

Approval ID: FILE E 238705



cUL Listed

Approval ID: FILE E 238705



cUL Listed

Approval ID: FILE E 238705



UL Listed

Approval ID: FILE E 238705



cUL Listed

Approval ID: FILE E 196811



UL Listed

Approval ID: FILE E 196811



UL Listed

Approval ID: FILE E 196811



cUL Listed

Approval ID: FILE E 196811

cULus Listed

cULus Listed

Wireless module - FL BT EPA 2



1005869

<https://www.phoenixcontact.com/pc/products/1005869>

Classifications

ECLASS

ECLASS-9.0	19170101
ECLASS-10.0.1	19170101
ECLASS-11.0	19170101

ETIM

ETIM 8.0	EC000515
----------	----------

UNSPSC

UNSPSC 21.0	43201400
-------------	----------

Wireless module - FL BT EPA 2



1005869

<https://www.phoenixcontact.com/pc/products/1005869>

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Wireless module - FL BT EPA 2

1005869

<https://www.phoenixcontact.com/pc/products/1005869>



Accessories

DIN rail adapter

DIN rail adapter - FL EPA RMS - 2701133

<https://www.phoenixcontact.com/pc/products/2701133>

Set for mounting devices with EPA design on a DIN rail



Mounting adapter

Mounting adapter - FL EPA WMS - 2701134

<https://www.phoenixcontact.com/pc/products/2701134>

Set for mounting devices with EPA design to wall or mast, including mast clips for a diameter of 25 - 85 mm, can be moved on two axes for optimum alignment, stainless steel



Wireless module - FL BT EPA 2

1005869

<https://www.phoenixcontact.com/pc/products/1005869>

RJ45 connector

RJ45 connector - VS-08-RJ45-5-Q/IP20 - 1656725

<https://www.phoenixcontact.com/pc/products/1656725>




RJ45 connector, degree of protection: IP20, number of positions: 8, 1 Gbps, CAT5 (IEC 11801:2002), material: PA, connection method: IDC fast connection, connection cross section: AWG 26- 23, cable outlet: straight, color: traffic grey A RAL 7042, Ethernet

Bus system cable

Bus system cable - SAC-4P-M12MSD/ 2,0-931 - 1569391

<https://www.phoenixcontact.com/pc/products/1569391>



Bus system cable, Ethernet CAT5 (100 Mbps), 4-position, PUR halogen-free, water blue RAL 5021, shielded, Plug straight M12, coding: D, on free cable end, cable length: 2 m

Wireless module - FL BT EPA 2


1005869

<https://www.phoenixcontact.com/pc/products/1005869>

Bus system cable

Bus system cable - SAC-4P-M12MSD/ 5,0-931 - 1569401

<https://www.phoenixcontact.com/pc/products/1569401>



Bus system cable, Ethernet CAT5 (100 Mbps), 4-position, PUR halogen-free, water blue RAL 5021, shielded, Plug straight M12, coding: D, on free cable end, cable length: 5 m

Network cable

Network cable - NBC-MSD/ 1,0-93E/R4AC SCO - 1407360

<https://www.phoenixcontact.com/pc/products/1407360>



Network cable, Ethernet CAT5 (100 Mbps), 4-position, shielded (Advanced Shielding Technology), Plug straight M12 / IP67, coding: D, on Plug straight RJ45 / IP20, cable length: 1 m

Wireless module - FL BT EPA 2

1005869

<https://www.phoenixcontact.com/pc/products/1005869>

Network cable

Network cable - NBC-MSD/ 2,0-93E/R4AC SCO - 1407361

<https://www.phoenixcontact.com/pc/products/1407361>



Network cable, Ethernet CAT5 (100 Mbps), 4-position, shielded (Advanced Shielding Technology), Plug straight M12 / IP67, coding: D, on Plug straight RJ45 / IP20, cable length: 2 m

Network cable

Network cable - NBC-MSD/ 5,0-93E/R4AC SCO - 1407362

<https://www.phoenixcontact.com/pc/products/1407362>



Network cable, Ethernet CAT5 (100 Mbps), 4-position, shielded (Advanced Shielding Technology), Plug straight M12 / IP67, coding: D, on Plug straight RJ45 / IP20, cable length: 5 m

Wireless module - FL BT EPA 2

1005869

<https://www.phoenixcontact.com/pc/products/1005869>

Sensor/actuator cable

Sensor/actuator cable - SAC-4P- 2,0-PUR/M12FS - 1533576

<https://www.phoenixcontact.com/pc/products/1533576>



Sensor/actuator cable, 4-position, PUR halogen-free, black-gray RAL 7021, free cable end, on Socket straight M12, coding: A, cable length: 2 m

Sensor/actuator cable

Sensor/actuator cable - SAC-4P- 3,0-PUR/M12FS - 1668111

<https://www.phoenixcontact.com/pc/products/1668111>



Sensor/actuator cable, 4-position, PUR halogen-free, black-gray RAL 7021, free cable end, on Socket straight M12, coding: A, cable length: 3 m

Wireless module - FL BT EPA 2

1005869

<https://www.phoenixcontact.com/pc/products/1005869>

Sensor/actuator cable

Sensor/actuator cable - SAC-4P- 5,0-PUR/M12FS - 1668124

<https://www.phoenixcontact.com/pc/products/1668124>



Sensor/actuator cable, 4-position, PUR halogen-free, black-gray RAL 7021, free cable end, on Socket straight M12, coding: A, cable length: 5 m

Sensor/actuator cable

Sensor/actuator cable - SAC-4P-10,0-PUR/M12FS - 1683002

<https://www.phoenixcontact.com/pc/products/1683002>



Sensor/actuator cable, 4-position, PUR halogen-free, black-gray RAL 7021, free cable end, on Socket straight M12, coding: A, cable length: 10 m

Phoenix Contact 2022 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstraße 8
D-32825 Blomberg
+49 (0) 5235-3 00
info@phoenixcontact.com