

## FEATURES

- Use for controlling industrial devices and small machines
- Fitted with a momentary changeover switch
- Complete with 2 metres of cable
- Sealed to IP40
- Single pedal foot operated switches
- Durable and reliable with steel housing for long life
- Operating Temperature: -5°C to 40°C

## RS PRO General Purpose Momentary Metal Foot Switch - Mild Steel Case Material, SP-CO, 3 A Contact Current, 250V Contact

RS Stock No.: 254-2348



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description ATTRIBUTE 1

RS PRO single pole versatile foot switch with a durable steel housing for long life and high reliability. The foot switches have a low profile that helps eliminate operator fatigue, with only a small amount of pressure required to operate.

This range of foot pedal switches includes:

254-2348 - Black robust metal foot switch, Momentary

251-2230- Black/White, Momentary

## General Specifications

<b>Contact Configuration</b>	SP-CO
<b>Switch Operation</b>	Momentary
<b>Case Material</b>	Mild Steel
<b>Switch Environment</b>	General Purpose
<b>Contact Material</b>	Silver
<b>Colour</b>	Black
<b>Applications</b>	Foot switches are commonly used in applications where hands-free control is more practical or safer. They can be found on: Industrial machinery and smaller power tools, Hospital beds, Dentist Chairs, Lamps

## Electrical Specifications

<b>Contact Voltage Rating (AC)</b>	250V
<b>Contact Voltage Rating (DC)</b>	24V
<b>Contact Current Rating</b>	3A

## Mechanical Specifications

<b>Length</b>	90mm
<b>Height</b>	24mm
<b>Dimensions</b>	90mm x 66mm x 24mm
<b>Width</b>	66mm

## Operation Environment Specifications

<b>Operating Temperature</b>	-5°C to 40°C
------------------------------	--------------

## Protection Category

<b>IP Rating</b>	IPX2
------------------	------

## Approvals

<b>Standards Met</b>	2014/35/EU, EN 60950
<b>Compliance/Certifications</b>	EN 61058-2-1; EN 61058; EN 60601-1; EN 6095, RoHS





## Outline Dimensions

