



SIMATIC S7-1500 Digital input module, DI 16x24 V DC BA, 16 channels in groups of 16, input delay typ. 3.2 ms, input type 3 (IEC 61131); Delivery incl. front connector Push-in

General information	
Product type designation	DI 16 x 24 V DC BA
HW functional status	From FS01
Firmware version	V1.0.0
<ul style="list-style-type: none"> FW update possible 	Yes
Product function	
<ul style="list-style-type: none"> I&M data 	Yes; I&M0 to I&M3
<ul style="list-style-type: none"> Isochronous mode 	No
<ul style="list-style-type: none"> Prioritized startup 	Yes
Engineering with	
<ul style="list-style-type: none"> STEP 7 TIA Portal configurable/integrated from version 	V13 / V13
<ul style="list-style-type: none"> STEP 7 configurable/integrated from version 	V5.5 SP3 / -
<ul style="list-style-type: none"> PROFIBUS from GSD version/GSD revision 	V1.0 / V5.1
<ul style="list-style-type: none"> PROFINET from GSD version/GSD revision 	V2.3 / -
Operating mode	
<ul style="list-style-type: none"> DI 	Yes
<ul style="list-style-type: none"> Counter 	No
<ul style="list-style-type: none"> MSI 	Yes
Supply voltage	
Rated value (DC)	24 V
permissible range, lower limit (DC)	19.2 V
permissible range, upper limit (DC)	28.8 V
Power	
Power available from the backplane bus	1.05 W
Power loss	
Power loss, typ.	1.8 W
Digital inputs	
Number of digital inputs	16
Digital inputs, parameterizable	No
Source/sink input	P-reading
Input characteristic curve in accordance with IEC 61131, type 3	Yes
Input voltage	
<ul style="list-style-type: none"> Rated value (DC) 	24 V
<ul style="list-style-type: none"> for signal "0" 	-30 to +5 V
<ul style="list-style-type: none"> for signal "1" 	+11 to +30V
Input current	
<ul style="list-style-type: none"> for signal "1", typ. 	2.7 mA

Input delay (for rated value of input voltage)	
for standard inputs	
— parameterizable	No
— at "0" to "1", min.	3 ms
— at "0" to "1", max.	4 ms
— at "1" to "0", min.	3 ms
— at "1" to "0", max.	4 ms
for interrupt inputs	
— parameterizable	No
for technological functions	
— parameterizable	No
Cable length	
• shielded, max.	1 000 m
• unshielded, max.	600 m
Encoder	
Connectable encoders	
• 2-wire sensor	Yes
— permissible quiescent current (2-wire sensor), max.	1.5 mA
Interrupts/diagnostics/status information	
Diagnostics function	No
Alarms	
• Diagnostic alarm	No
• Hardware interrupt	No
Diagnoses	
• Monitoring the supply voltage	No
• Wire-break	No
• Short-circuit	No
Diagnostics indication LED	
• RUN LED	Yes; green LED
• ERROR LED	Yes; red LED
• Monitoring of the supply voltage (PWR-LED)	No
• Channel status display	Yes; green LED
• for channel diagnostics	No
• for module diagnostics	No
Potential separation	
Potential separation channels	
• between the channels	No
• between the channels, in groups of	16
• between the channels and backplane bus	Yes
Isolation	
Isolation tested with	707 V DC (type test)
Standards, approvals, certificates	
Suitable for safety functions	No
Ambient conditions	
Ambient temperature during operation	
• horizontal installation, min.	-30 °C; from FS04
• horizontal installation, max.	60 °C
• vertical installation, min.	-30 °C; from FS04
• vertical installation, max.	40 °C
Altitude during operation relating to sea level	
• Installation altitude above sea level, max.	5 000 m; Restrictions for installation altitudes > 2 000 m, see manual
Dimensions	
Width	25 mm
Height	147 mm
Depth	129 mm
Weights	
Weight, approx.	230 g
Other	

Note:

Supplied incl. 40-pole push-in front connectors

last modified:

6/24/2021 