

Drawer cabinet system 800 B with 13 SOFT-CLOSE drawers

Depth 800 mm, width 1022 mm


Application:

Particularly suitable for careful storage of delicate, sensitive tools and parts in drawers.

Advantage:

- The damping system brakes the drawer while closing; it closes the drawer smoothly and soundlessly by means of the self-closing mechanism
- Impact load on tools and parts stored in the drawer is reduced to a minimum due to the smooth-closing drawers
- High quality - made in Germany

Art. no.	50315 782
Brand	HK
Manufacturer Part Number	50315782
Number of drawers	13 PCS
Height	1036 mm
Width	1022 mm
Depth	800 mm
Height x width x depth	1036 x 1022 x 800 mm
Drawer width (inner dimension) x drawer depth (inner dimension)	900 x 700 mm
Drawer with slots	Yes
Perforated drawer base	Yes
Load-carrying capacity per drawer	200 kg
Drawer surface	0.63 m ²
Pullout type	Full extension
With SOFT-CLOSE closing function	Yes
With single pull-out safety brake	Yes
Central locking	Yes
Material of cover panel	Wood, plastic-coated
Cabinet colour	Optional
Colour of front	Optional
Surface	Powder-coated
Functions	RFID possible
Model	B8 32/13
Overall surface	8.19 m ²
Lock type	DOM® locking system
Material	Sheet steel
Gross Weight	311.000 kg
Product Group	5BB



EAN

4053625050567