



MSD Platinum (Touring/Stage)

MSD Platinum 16 R 1CT/8

The MSD Platinum lamps open up new levels of creative freedom in entertainment lighting, with powerful, compact and brilliantly intense light. Their compact, lightweight design provides the freedom to create smaller, lighter luminaires – for use at any location on stage. And their short arc, high color temperature and innovative reflector produce a sparkling, high beam intensity for outstanding color reproduction. They also offer long and reliable lifetime, high efficacy and fast replacement times. It all adds up to an intensely exciting creative experience.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information		Correlated Color Temperature (Nom)		8000 K	
Cap-Base	- [-]	Color Rendering Index (Nom)		-	
Operating Position	UNIVERSAL [Any or Universal (U)]	Operating and Electrical			
Main Application	Stage/Touring	Power (Nom)	330 W		
Life to 50% Failures (Nom)	1500 h	Controls and Dimming			
System Description	Reflector E21.9 TCM	Dimmable	Yes		
Light Technical		Mechanical and Housing			
Color Code	2	Cap-Base Information	-		
Luminous Flux (Min)	14300 lm				
Luminous Flux (Nom)	16000 lm				
Chromaticity Coordinate X (Nom)	299				
Chromaticity Coordinate Y (Nom)	303				

MSD Platinum (Touring/Stage)

Luminaire Design Requirements


Bulb Temperature (Max)	900 °C
Pinch Temperature (Max)	350 °C

Product Data

Full product code	871829170438600
Order product name	MSD Platinum 16 R 1CT/8
EAN/UPC - Product	8718291704386

Order code	928195205314
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	8
Material Nr. (12NC)	928195205314
Net Weight (Piece)	0.080 kg

Dimensional drawing



MSD Platinum 16 R

Product	D (max)	O	C (max)
MSD Platinum 16 R 1CT/8	58.5 mm	1.3 mm	66.4 mm

Photometric data

