



### Model Number

**LLE 18/30-2,3-1,0-WC0**

Glass fibre optic - thru beam with metal-silicone-covering

### Series

Fiber optic amplifiers

Device series RL5-LL GLV30

### Description

#### Attention:

Fibre optics must not be twisted or kinked. Excessive tensile loads will lead to destruction. Contact with petrol or organic solvents must be prevented.



### Technical data

#### General specifications

Fiber optic length	l	1000 mm
Fiber optic diameter	d	5.3 mm
Adapter form		18/30
End piece		Side view / Periscope
Bending radius		min. 22 mm
Fiber bundle diameter		2.3 mm
Approvals		CE
Angle of divergence		approx. 68 °

#### Ambient conditions

Ambient temperature	-20 ... 95 °C (-4 ... 203 °F) [Adapter]
	-40 ... 180 °C (-40 ... 356 °F) [End head and Covering]
Storage temperature	-20 ... 85 °C (-4 ... 185 °F)

#### Mechanical specifications

Protection degree	IP65
Material	
Optical face	glass
Sheathing	Metal-silicon
Core	Glass fiber
End piece	Stainless steel 1.4305 / AISI 303
Adapter	Polyamide PA 6.6
Extraction force	at probe at 20°C: 120 N

### Dimensions

