


KQ1000



Electronic level sensor

KQ-5xxxNFPKG/IO



1 LED bar graph



Product characteristics

Electrical design	PNP/NPN; (parameterisable)
Communication interface	IO-Link
Dimensions [mm]	250 x 28 x 16.7

Application

Media	dry bulk material; aqueous solutions; oils
Cannot be used for	very adhesive media

KQ1000



Electronic level sensor

KQ-5xxxNFPKG/IO

Electrical data		
Operating voltage	[V]	10...30 DC; (18...30 DC: IO-Link)
Current consumption	[mA]	< 50
Protection class		III
Reverse polarity protection		yes
Max. power-on delay time	[ms]	1300
Inputs / outputs		
Number of inputs and outputs		Number of digital outputs: 3
Outputs		
Electrical design		PNP/NPN; (parameterisable)
Number of digital outputs		3
Permanent current rating of switching output DC	[mA]	200
Max. resistance switching output	[Ω]	8
Short-circuit protection		yes
Type of short-circuit protection		pulsed
Overload protection		yes
Detection zone		
Measuring range	[mm]	< 200
Measuring/setting range		
Detection range	[mm]	228
Set point SP	[%]	5...95
Reset point rP	[%]	4...94
In steps of	[%]	1
Accuracy / deviations		
Repeatability		2
	[% of the final value]	
Offset deviation		4
	[% of the final value]	
Resolution	[% of the final value]	1
Linearity deviation		1
	[% of the final value]	
Response times		
Response time	[ms]	1300

KQ1000



Electronic level sensor

KQ-5xxxNFPKG/IO

Interfaces		
Communication interface	IO-Link	
Transmission type	COM2 (38,4 kBaud)	
IO-Link revision	1.1	
SDCI standard	IEC 61131-9	
Profiles	Digital Measuring Sensor Profile, Common Profile	
SIO mode	yes	
Required master port type	A	
Process data analogue	1	
Process data binary	3	
Min. process cycle time [ms]	9.6	
IO-Link functions (cyclical)	function	bit length
	process value	16
	exponent	8
	device status	4
	binary switching information	3
IO-Link functions (acyclical)	direction of installation; limitation of sensor elements; sensitivity; minimum recognition threshold; Performance in case of a fault; error delay; Damping; LED_Modus; switch-on cycle counter; operating hours counter; switching cycles counter; min./max. process value; internal temperature; min./max. internal temperature; diagnostic data level	
Supported DeviceIDs	Type of operation	IO-Link device ID
	Default	924 d / 00 03 9C h
Note	For further information please see the IODD PDF file at "Downloads"	
Operating conditions		
Applications	DIN EN 60654-1 application class B2	
Ambient temperature [°C]	-20...80	
Storage temperature [°C]	-25...85	
Protection	IP 65; IP 67	
Tests / approvals		
EMC	DIN EN 61000-6-4 30 - 230 MHz	40 dB μ V/m QP / 10 m distance
	230 - 1 GHz	47 dB μ V/m QP / 10 m distance
	DIN EN 61000-4-2	\pm 25 kV AD / \pm 25 kV CD
	DIN EN 61000-4-3	80 MHz - / 1 GHz 10 V/m
	DIN EN 61000-4-4	\pm 2.5 kV / 5 kHz
		\pm 2.5 kV / 100 kHz
DIN EN 61000-4-6	10 V	
Shock resistance	EN 60068-2-27	15 g / 11 ms
Vibration resistance	EN 60068-2-6	5 g (10...2000 Hz)
MTTF [years]	290.43	
UL approval	Ta	-25...60 °C
	Enclosure type	Type 1
	voltage supply	Limited Voltage/Current
	UL Approval no.	D005
	File number UL	E174191


KQ1000



Electronic level sensor

KQ-5xxxNFPKG/IO

Mechanical data		
Weight [g]	432	
Dimensions [mm]	250 x 28 x 16.7	
Materials	PBT; PC;	
Displays / operating elements		
Display	operation	1 x LED, green
	switching status	3 x LED, yellow
	function	20 x LED, green
Accessories		
Accessories (supplied)	adhesive tape: 1 x 1,2 x 23 x 240 mm Mounting adapter, E12675	
Accessories (optional)	Mounting adapter, E12676 Fixing strap, E10880	
Remarks		
Remarks	when used on IO-Link class B masters switching outputs OUT2, OUT3 have to be switched off	
Pack quantity	1 pcs.	
Electrical connection		
Cable: 2 m, PUR; 5 x 0.34 mm ²		
Connection		



Core colours	
BN	brown
GY	grey switching output 3
WH	white switching output 2
BK	black switching output 1 / IO-Link
BU	blue