



21HDG

ERGO™ Heavy Duty Side Cutting Pliers with Self Opening Dual-Component Handle and Phosphate Finish



PRODUCT DETAILS

- Two-component ERGO™ handles: thermoplastic surface on tough polypropylene provides superior grip
- Heavy-duty side cutting pliers developed according to the scientific ERGO™ process
- Suitable for cutting Cu, Fe+ and piano wire
- Distance from joint to centre of cutting edges is reduced for greater leverage and increased cutting capacity
- Equipped with a patented return spring featuring an on/off function
- High-performance alloy steel
- Phosphate finish, anti-corrosion treated
- Heavy-duty cutting edge
- Screw joint that provides excellent running and accurate alignment of the cutting edges
- Distance from the joint to the centre of the cutting edges is reduced: giving greater leverage and increased cutting capacity
- Metal frame designed to enhance accessibility in confined spaces
- Equipped with a patented return spring featuring an on/off function
- Induction hardened cutting edges
- Maximum comfort with minimum effort due to the ergonomic design
- Comfortable two-component handles giving an excellent grip
- Self-opening handles when spring activated



Follow the Fish!



PRODUCT ATTRIBUTES

Product	✘	✘	✘	✘	✘	✘	✘	✘
21HDG-140	140 mm	15.9 mm	21 mm	8 mm	2.0 mm	2.2 mm	2.2 mm	110 g
21HDG-160	160 mm	18 mm	23 mm	9 mm	2.1 mm	2.5 mm	2.5 mm	150 g
21HDG-180	180 mm	19.8 mm	25 mm	10 mm	2.3 mm	2.8 mm	2.8 mm	210 g
21HDG-200	200 mm	22.4 mm	27 mm	10 mm	2.8 mm	3.2 mm	3.0 mm	270 g
21HDG-140IP	140 mm	15.9 mm	21 mm	8 mm	2.0 mm	2.2 mm	2.2 mm	110 g
21HDG-160IP	160 mm	18 mm	23 mm	9 mm	2.1 mm	2.5 mm	2.5 mm	150 g
21HDG-180IP	180 mm	19.8 mm	25 mm	10 mm	2.3 mm	2.8 mm	2.8 mm	210 g
21HDG-200IP	200 mm	22.4 mm	27 mm	10 mm	2.8 mm	3.2 mm	3.0 mm	270 g

