

# Part Number: 10GX UTP LSZH PATCH CORDS



10GX Patch Cord UTP LSZH

# **Product Description**

10GX Copper Patch Cord UTP LSZH

# **Technical Specifications**

#### **Product Overview**

Environmental Space:	Indoor Rated (Not Riser or Plenum)
Suitable Applications:	Horizontal and building cabling. Support current and future Category 6a and 6 applications, such as: 10GBase-T (10 Gigabit Ethernet), 100Base-T (Gigabit Ethernet), 100 Base-T, 10 Base-T, FDDI, ATM

## **Physical Characteristics (Overall)**

#### Conductor

AWG	Stranding	Material	Nomina	l Diameter	No. of Pairs
26	Stranded	Copper	6.1 mm		4
Total Number of Pairs: 4					
Condu	uctor Size:			26 AWG	

#### Insulation

Material
FPE - Foamed Polyethylene

#### Inner Shield Material

Element	Type	Material
Floating shielded pair	Tape	Laminated aluminum-polyester

#### Inner Jacket Material



#### **Outer Shield Material**

Туре	Material	Coverage [%]
Braid (Floating)	TC - Tinned Copper	30 %

# Outer Jacket Material

## Connectors

## Materials

Description	Material	Туре
Plug	Polycarbonate	RJ45
Boot	PVC	Snagless
Front Connection	Phosphor Bronze with 50u inch Gold over Nickel Plating	Blades

Nominal Diameter

#### **Electrical Characteristics**

Dielectric Strength:	2.5 KV DC
Current Rating:	1 A
Insulation Resistance:	5000 MOhm*km
Max Contact Resistance:	20 mOhm

#### Voltage

# Voltage Rating [V]

72 V DC

Performance Footnote1:	There is 1dB margin on NEXT and RL guaranteed compared to ISO/IEC 11801-1:2017
Performance Footnote2:	The performance data below 4Mhz or above 500Mhz are for information only.

# **Temperature Range**

Installation Temp Range:	0°C To +50°C
Operating Temp Range:	-20°C to +60°C

## **Mechanical Characteristics**

Min Bend Radius (Overall Cable):	25 mm
Plug /Jack Compatibility:	RJ45

#### Termination Interface

Termination	Connection	Durabilities
RJ45	Mated Connection	750 Cycles

# **Standards**

ISO/IEC Compliance:	ISO/IEC 11801-1:2017
Data Category:	Category 6A
Telecommunications Standards:	ISO/IEC 11801-1:2017; EN 50173-1 Amd 1 Caregory 6A; ANSI/TIA/EIA 568 C.2 Category 6A

# **Applicable Environmental and Other Programs**

EU RoHS Compliance Date (yyyy-mm-dd):	2013-01-25

# Suitability

#### **Part Number**

|--|

## Variants

Item #	Color	Length
CA24100001M	Black	1 m
CA24100002M	Black	2 m
CA24100003M	Black	3 m
CA24100005M	Black	5 m
CA24100007M	Black	7 m
CA24100010M	Black	10 m
CA24100015M	Black	15 m
CA241000D5M	Black	0.5 m
CA24106001M	Blue	1 m
CA24106002M	Blue	2 m
CA24106003M	Blue	3 m
CA24106004M	Blue	4 m
CA24106005M	Blue	5 m
CA24106006M	Blue	6 m
CA24106010M	Blue	10 m
CA24106015M	Blue	15 m
CA24106016M	Blue	16 m
CA241060D5M	Blue	0.5 m
CA241060D3M	Blue	0.3 m
CA24106020M	Blue	20 m

CA24108001M	Gray	1 m
CA24108002M	Gray	2 m
CA24108003M	Gray	3 m
CA24108005M	Gray	5 m
CA24108007M	Gray	7 m
CA24108010M	Gray	10 m
CA24108012M	Gray	12 m
CA24108015M	Gray	15 m
CA24108016M	Gray	16 m
CA24108020M	Gray	20 m
CA24108050M	Gray	50 m
CA241080D5M	Gray	0.5 m
CA241084D6M	Gray	4.6 m
CA24105001M	Green	1 m
CA24105002M	Green	2 m
CA24105003M	Green	3 m
CA24105005M	Green	5 m
CA24105010M	Green	10 m
CA24105016M	Green	16 m
CA241050D5M	Green	0.5 m
CA24103001M	Orange	1 m
CA24103002M	Orange	2 m
CA24103003M	Orange	3 m
CA24103005M	Orange	5 m
CA24103010M	Orange	10 m
CA24102001M	Red	1 m
CA24102001W	Red	2 m
CA24102002W	Red	3 m
CA24102005M		5 m
	Red	
CA24102010M	Red	10 m
CA24102015M	Red	15 m
CA24102016M	Red	16 m
CA241020D5M	Red	0.5 m
CA24107001M	Violet	1 m
CA24107002M	Violet	2 m
CA24107003M	Violet	3 m
CA24107005M	Violet	5 m
CA24107010M	Violet	10 m
CA24109001M	White	1 m
CA24109002M	White	2 m
CA24109003M	White	3 m
CA24109005M	White	5 m
CA24109010M	White	10 m
CA241090D5M	White	0.5 m
CA24104001M	Yellow	1 m
CA24104002M	Yellow	2 m
CA24104003M	Yellow	3 m
CA24104005M	Yellow	5 m
CA24104010M	Yellow	10 m
CA241040D5M	Yellow	0.5 m

© 2019 Belden, Inc

All Rights Reserved

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.