

Heavy-duty cabinet without central partition

With solid sheet metal doors, with drawers and shelves

RasterPlan

Application:

For a total loading capacity of up to 1.65 t for very heavy loads, particularly suitable for storage of the heaviest tools, such as embossing and punching dies.

Execution:

- Extremely stable welded steel structure with brazed corners, with or without central partition
- Smooth fronts due to flush overlay doors, opening angle more than 200°, continuous rod guiding
- Doors can be locked simultaneously with a triple-point security cylinder lock, incl. 2 keys
- Cabinet base can carry a load of up to 400 kg

Delivery:

Additional door designs, e.g. perforated or slotted panel doors and sidewall lining, pull-out blocks for drawers and suitable insert material with compartment dividers, additional group or main keys and further paint colours deliverable upon request.



| | |
|--|--|
| Art. no. | 50047 221 |
| Brand | RASTERPLAN |
| Manufacturer Part Number | 1471.01.2016 |
| Door design | Full-sheet panel |
| Width | 1000 mm |
| Depth | 600 mm |
| Height | 1110 mm |
| Number of shelves | 1 PCS |
| Shelf width | 1000 mm |
| Shelf depth | 600 mm |
| Load-carrying capacity per shelf | 160 kg |
| Number of drawers | 2 PCS |
| Drawer front height | 2 x 100 mm |
| Drawer width (inner dimension) | 889 mm |
| Drawer depth (inner dimension) | 483 mm |
| Load-carrying capacity per drawer | 110 kg |
| Pullout type | Full extension |
| With partition wall | No |
| Load-carrying capacity | 1650 kg |
| Central locking | Yes |
| Lock type | Twist-grip lock with three-point fastening |
| Material | Sheet steel |
| Colour of front | Gentian blue RAL 5010 |
| Surface | Powder-coated |
| Cabinet colour | Light grey RAL 7035 |
| Gross Weight | 86.500 kg |
| Product Group | 5AC |

EAN

4251142218976