

MVP12, 8XM12, MOSA, PLUGGABLE CABLE



5.0m PUR-JB 16x0,34+5x0,75

quick connection elements included
with LED for digital PNP-signals 24 V DC
8-way, 5-pole, MOSA
PUR/PVC
5.0 m
potentially separated


Further cable lengths on request. Plastic housings with good resistance against chemicals and oils. The resistance to aggressive media should be individually tested for your application. Further details on request.

[Link to Product](#)

Illustration



for 2 signals per port



Product may differ from Image

Technical Data

Operating voltage	24 V DC
Signal per port	2
Operating current per contact	max. 4 A
Total current	max. 2 × 8 A
Connection cross section	0.25...0.5 mm ²
Outer wire diameter	Cap nut
Housing	Plastic, flame retardant
Protection	IP67 inserted and tightened (EN 60529)
Locking of ports	Cap nut

Cables

No./diameter of wires	16×0.34 + 5×0.75 mm ²
C-track properties	2 Mio.
Material (jacket)	PUR/PVC
Outer diameter	approx. 12.5 mm
Bend radius (moving)	12 × outer Ø
Cable number	404

General data

Temperature range	-20...+80 °C
-------------------	--------------

The information in this brochure has been compiled with the utmost care.

Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 05/15

Murrelektronik GmbH | Falkenstraße 3, 71570 Oppenweiler | Fon +49 (71 91) 47-0, Fax +49 (71 91) 47-491000 | shop@murrelektronik.de | shop.murrelektronik.de

Dimensions H x W x D	43x50.2x170 mm
----------------------	----------------

Contact layout

Contact 1	(+)
-----------	-----

Contact 2	(NC)/(S2)
-----------	-----------

Contact 3	(-)
-----------	-----

Contact 4	(NO)/(S1)
-----------	-----------

Contact 5	(Earth)
-----------	---------

LED display	LED (green): Power / LED (yellow): (S1/S2)
-------------	--

Commercial data

country of origin	DE
-------------------	----

customs tariff number	85369010
-----------------------	----------

minimum order quantity	1
------------------------	---