



Figure similar

MAINS CHOKE F.FU; PHASES:3; UN1(V):480;  
 ITHMAX 1(A) / F1(HZ):560 /60; I LN (A):504; UK(%):2;  
 LN(MH):0,0252; TA/ISOKL:40 /H; IP00; TYPE OF  
 TERMINALS:FLAT-TYPE TERMINAL; EN 61558-2-20  
 >UL/CSA-RECOGNIZED< >CHOKE<

### General technical data:

<b>Product designation</b>		Netzdrossel f. FU
<b>product brand name</b>		SIDAC
<b>Phase number</b>		3
<b>Type of voltage</b>		AC
<b>Operating voltage Rated value</b>	V	400, 480
<b>Operating frequency Rated value</b>	Hz	50 ... 60
<b>Current</b>		
• with AC		
— Rated value	A	504
— maximum	A	560
<b>Inductivity Rated value</b>	H	0.000025
<b>Relative inductive drop in voltage on the measurement level current, voltage and frequency</b>	%	2
<b>Active power loss of the coil</b>	W	216
<b>Active power loss of the iron core</b>	W	115

### Mechanical data:

<b>Type of electrical connection for main current circuit</b>		flat connector
<b>Width</b>	m	0.3
<b>Height</b>	m	0.269
<b>Depth</b>	m	0.221

### Ambient conditions:

<b>Thermal class acc. to IEC 60085</b>		H
<b>Ambient temperature Rated value</b>	°C	40
<b>Protection class IP</b>		IP00

## Certificates/ approvals:

**General Product Approval**



**Declaration of Conformity**



## Further information

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/industrial-controls/catalogs>

**Industry Mall (Online ordering system)**

<http://www.siemens.com/industrymall>

**Cax online generator**

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=4EU30525UA000AA0>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/en/ps/4EU30525UA000AA0>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=4EU30525UA000AA0&lang=en](http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=4EU30525UA000AA0&lang=en)

**last modified:**

16.03.2015