



SIMATIC DP, ELECTRONIC MODULE 2 AO I HIGH FEATURE FOR ET 200S, 15 MM WIDE, CYCLE TIME PER MODULE: 0.5MS, +/- 20MA; 15 BIT + SIGN, 4 .. 20MA; 15 BIT, OPERATIONAL LIMITS +/- 0.05% WITH LED SF (GROUP FAULT)

### Supply voltage

#### Load voltage L+

- |                               |      |
|-------------------------------|------|
| • Rated value (DC)            | 24 V |
| • Reverse polarity protection | Yes  |

### Input current

- |   |       |
|---|-------|
| from load voltage L+ (without load), max. | 80 mA |
| from backplane bus 3.3 V DC, max.         | 10 mA |

### Power losses

- |                  |       |
|------------------|-------|
| Power loss, max. | 1.2 W |
|------------------|-------|

### Address area

#### Address space per module

- |                                  |        |
|----------------------------------|--------|
| • Address space per module, max. | 4 byte |
|----------------------------------|--------|

### Analog outputs

- |                                       |        |
|---------------------------------------|--------|
| Number of analog outputs              | 2      |
| Current output, no-load voltage, max. | 18 V   |
| Cycle time (all channels) max.        | 0.5 ms |

#### Output ranges, current

- |                    |     |
|--------------------|-----|
| • -20 mA to +20 mA | Yes |
| • 4 mA to 20 mA    | Yes |

#### Connection of actuators

- |   |     |
|---|-----|
| • for current output two-wire connection  | Yes |
| • for current output four-wire connection | No  |

#### Load impedance (in rated range of output)

• with current outputs, max.	500 $\Omega$
• with current outputs, inductive load, max.	1 mH
<b>Destruction limits against externally applied voltages and currents</b>	
• Current, max.	50 mA
<b>Cable length</b>	
• shielded, max.	200 m; 100m if Twa < 2ms
<b>Analog value creation</b>	
<b>Integration and conversion time/resolution per channel</b>	
• Resolution with overrange (bit including sign), max.	16 bit
<b>Settling time</b>	
• for resistive load	0.3 ms
• for capacitive load	1 ms
• for inductive load	0.5 ms
<b>Errors/accuracies</b>	
Output ripple (based on output area, bandwidth 0 to 50 kHz), (+/-)	0.02 %
Linearity error (relative to output range), (+/-)	0.01 %
Temperature error (relative to output range), (+/-)	0.003 %/K
Crosstalk between the outputs, min.	60 dB
Repeat accuracy in steady state at 25 °C (relative to output area), (+/-)	0.01 %
<b>Operational limit in overall temperature range</b>	
• Current, relative to output area, (+/-)	0.1 %
<b>Basic error limit (operational limit at 25 °C)</b>	
• Current, relative to output area, (+/-)	0.05 %
<b>Isochronous mode</b>	
Isochronous operation (application synchronized up to terminal)	Yes
<b>Interrupts/diagnostics/status information</b>	
Substitute values connectable	Yes
<b>Diagnostic messages</b>	
• Diagnostic information readable	Yes
• Wire break	Yes
• Group error	Yes
<b>Diagnostics indication LED</b>	
• Group error SF (red)	Yes
<b>Parameter</b>	
Remark	7 byte
Output type/range	deactivated / +/-20 mA / 4 to 20 mA
Diagnosis: wire break	Disable / enable

Interference frequency suppression	Disable / enable
Group diagnostics	Disable / enable
Behavior on CPU/Master STOP	Output current and de-energized/substitute a value/keep last value

### Galvanic isolation

Galvanic isolation analog outputs	
• Galvanic isolation analog outputs	Yes
• between the channels	No
• between the channels and the backplane bus	Yes
• between the channels and the load voltage L+	Yes

### Permissible potential difference

between MANA and M internally (UISO)	75V DC/60V AC
--------------------------------------	---------------

### Isolation

Isolation checked with	500 V DC
------------------------	----------

### Dimensions

Width	15 mm
Height	81 mm
Depth	52 mm

### Weights

Weight, approx.	40 g
-----------------	------

**last modified:** 12.03.2015